



MSR Gold™ FastFit

MSR Gold™ 1500 FastFit 1CT/4

All lamps burn out eventually, but when this happens with single ended MSR Gold™ FastFit, it is replaced in seconds – thanks to the specially designed lamp base and lamp holder. This lamp provides a high beam intensity of pure, white light for a truly illuminating performance, while the gold-plated caps provide superior heat protection and prevent premature failure. P3 technology allows use in any position and at higher temperatures, further extending lamp life and consistency of high-quality light output. Also, because the FastFit design is applied to Philips Halogen lamps, switching between lamp technologies can be done quickly and easily. The Philips MSR Gold™ 1200 FastFit can be operated in a lamp wattage range between 800W and 1400W.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General information		Operating and electrical	
Base	PGJX50 [PGJX50]	Chromaticity Coordinate X (Nom)	323
Operating Position	Universal [Universal]	Chromaticity Coordinate Y (Nom)	333
Main Application	Entertainment	Correlated Color Temperature (Nom)	6000 K
Life to 50% Failures (Nom)	750 h	Luminous Efficacy (rated) (Nom)	80 lm/W
System Description	FastFit	Color Rendering Index (Nom)	80
Light technical		Power (Rated) (Nom)	1500 W
Initial lumen (Min)	100600 lm	Lamp Current (Nom)	15.3 A
Initial lumen (Nom)	120000 lm		

MSR Gold™ FastFit

Ignition Supply Voltage (Min)	198 V
Controls and dimming	
Dimmable	Yes
Mechanical and housing	
Cap-Base Information	PGJX50
Luminaire design requirements	
Bulb Temperature (Max)	1742 °F
Pinch Temperature (Max)	932 °F

Product data	
Order product name	MSR Gold™ 1500 FastFit 1CT/4
EAN/UPC - Product	8718291221340
Order code	286971
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	928107305115
Copy Net Weight (Piece)	0.289 lb


Dimensional drawing




Product	D (max)	O	L (min)	L (max)	L	C (max)	F
MSR Gold™ 1500 FastFit 1CT/4	1-1/8 in	1/4 in	2-9/16 in	2-5/8 in	2-9/16 in	5-1/16 in	2 in

MSR Gold™ 1500 FastFit 1CT/4

Photometric data



XDPB_XDMSR_0002-Spectral power distribution B/W



XDPO_XDMSR_0002-Spectral power distribution Colour

