

PHILIPS

Lighting



MSR

MSR 575/2 10H 1CT/4

The high color rendering index of the single ended MSR series ensures that everyone in the audience can enjoy the true colors of the scenery, the stage props, the players and their costumes – in fact everything that is on stage can be made bright and vivid in daylight quality light. Also, thanks to the single ended lamp concept, the luminaire has optimal light collection and direction possibilities to help ensure brightness on stage exactly where and when it is needed. In addition, the MSR can be used in any burning position for easy set-up and convenience.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury. Manage in Accord with Disposal Laws. See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information		Operating and Electrical	
Base	GX9.5 [GX9.5]	Luminous Efficacy (Rated) (Min)	75 lm/W
Operating Position	Universal [Universal]	Luminous Efficacy (rated) (Nom)	83 lm/W
Main Application	Studio/Disco	Color Rendering Index (Nom)	70
Life to 50% Failures (Nom)	1000 h	Operating and Electrical	
System Description	Cold Strike	Power (Rated) (Nom)	575 W
Light Technical		Lamp Current (Nom)	6.75 A
Color Code	2	Ignition Supply Voltage (Min)	207 V
Initial lumen (Min)	42750 lm	Controls and Dimming	
Initial lumen (Nom)	47500 lm	Dimmable	No
Chromaticity Coordinate X (Nom)	302		
Chromaticity Coordinate Y (Nom)	320		
Correlated Color Temperature (Nom)	6990 K		

MSR

Mechanical and Housing

Cap-Base Information	20mm (20)
----------------------	-----------

Luminaire Design Requirements


Bulb Temperature (Max)	700 °C
Pinch Temperature (Max)	350 °C

Product Data

Order product name	MSR 575/2 10H 1CT/4
--------------------	---------------------

EAN/UPC - Product	8718291221272
Order code	287078
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	928171605115
Net Weight (Piece)	0.057 kg


Dimensional drawing




MSR 575/2 10H

Product	D (max)	O	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSR 575/2	30 mm	7.0	64 mm	66 mm	65	125 mm	36 mm	35	34 mm
10H 1CT/4		mm			mm			mm	

Photometric data



XDPB_XDMSR_CS-Spectral power distribution B/W



XDPO_XDMSR_CS-Spectral power distribution Colour

