



MSR Gold™ SA Double Ended

MSR Gold™ 1200 SA/2 DE 1CT/4

To optimize the total lifetime of the double ended MSR Gold™ SA Double Ended lamps, the caps are plated with gold. This provides superior heat protection and thereby minimizes premature failure of the lamp and lamp holder, as well as ensuring extended consistent performance. In addition, the highly innovative P3 technology, developed by Philips, allows the lamp to be used at higher temperatures, which further extends service life and consistency of high-quality light output.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General information		Initial lumen (Nom)		100000 lm
Base	SFC10-4 [SFC10-4]	Chromaticity Coordinate X (Nom)	301	
Operating Position	Universal [Universal]	Chromaticity Coordinate Y (Nom)	316	
Main Application	Entertainment	Correlated Color Temperature (Nom)	7500 K	
Life to 50% Failures (Nom)	750 h	Luminous Efficacy (Rated) (Min)	75 lm/W	
System Description	SA/2 DE	Luminous Efficacy (rated) (Nom)	83 lm/W	
		Color Rendering Index (Nom)	85	
Light technical		Operating and electrical		
Color Code	- [Not Specified]	Power (Rated) (Nom)	1200 W	
Initial lumen (Min)	90000 lm			

MSR Gold™ SA Double Ended

Lamp Current (Nom)	13.6 A
Ignition Supply Voltage (Min)	198 V

Controls and dimming

Dimmable	No
----------	----

Mechanical and housing


Cap-Base Information	SFC10-4
----------------------	---------

Product data

Order product name	MSR Gold™ 1200 SA/2 DE 1CT/4
--------------------	------------------------------

EAN/UPC - Product	8718291221074
Order code	287250
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	928175305115
Copy Net Weight (Piece)	0.075 lb


Dimensional drawing




MSR Gold™ 1200 SA/2 DE 1CT/4

Product	D (max)	O	A (min)	A (max)	A	C (max)
MSR Gold™ 1200 SA/2 DE 1CT/4	7/8 in	5/16 in	4-1/2 in	4-9/16 in	4-9/16 in	5-3/8 in

Photometric data



XDPB_XDMSR_1200W_SA2-DE-Spectral power distribution B/W



XDPO_XDMSR_1200W_SA2-DE-Spectral power distribution Colour

MSR Gold™ SA Double Ended

