



# MSR Gold™ MiniFastFit (Touring/ Stage)

## MSR Gold™ 575/2 MiniFastFit 1CT/4

Thanks to the specially designed lamp base, the MSR Gold™ MiniFastFit takes just seconds to replace, to help ensure non-stop clubbing entertainment. In addition, the innovative gold plated pins ensure excellent current transfer to prolong lamp and lamp holder lifetimes and thereby reduce lamp replacement costs. Easy handling and small compact fixture designs are allowed by the lamps compact size, while the very short arc provides a high perceived brightness and high beam intensity.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury. Manage in Accord with Disposal Laws. See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050

### Product data


General Information		Initial lumen (Nom)	
Base	PGJX28 [ PGJX28]	Initial lumen (Nom)	38600 lm
Operating Position	Universal [ Universal]	Chromaticity Coordinate X (Nom)	296
Main Application	Entertainment	Chromaticity Coordinate Y (Nom)	315
Life to 50% Failures (Nom)	750 h	Correlated Color Temperature (Nom)	7500 K
System Description	MiniFastFit	Luminous Efficacy (rated) (Nom)	63 lm/W
		Color Rendering Index (Nom)	70
Light Technical		Operating and Electrical	
Color Code	2	Power (Rated) (Nom)	575 W
Initial lumen (Min)	34500 lm	Lamp Current (Nom)	10.2 A

# MSR Gold™ MiniFastFit (Touring/Stage)

Ignition Supply Voltage (Min)	198 V
<b>Controls and Dimming</b>	
Dimmable	Yes
<b>Mechanical and Housing</b>	
Cap-Base Information	PGJX28
<b>Luminaire Design Requirements</b>	
Bulb Temperature (Max)	950 °C
Pinch Temperature (Max)	400 °C
Pinch Temperature (Min)	300 °C

<b>Product Data</b>	
Order product name	MSR Gold™ 575/2 MiniFastFit 1CT/4
EAN/UPC - Product	8718291221098
Order code	287201
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	928184005115
Net Weight (Piece)	0.070 kg



## Dimensional drawing



MSR GOLD 575/2 MiniFastFit

Product	D (max)	O	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSR Gold™ 575/2 MiniFastFit 1CT/4	23.2 mm	3.5 mm	55 mm	57 mm	56 mm	112 mm	36.5 mm	36 mm	35.3 mm

## Photometric data



XDPB\_XDMSR\_0004-Spectral power distribution B/W

## MSR Gold™ MiniFastFit (Touring/Stage)

