



# MSR Gold™ MiniFastFit (Touring/ Stage)

## MSR Gold™ 400 MiniFastFit 1CT/16

Thanks to the specially designed lamp base, the MSR Gold™ MiniFastFit takes just seconds to replace, to help ensure non-stop clubbing entertainment. In addition, the innovative gold plated pins ensure excellent current transfer to prolong lamp and lamp holder lifetimes and thereby reduce lamp replacement costs. Easy handling and small compact fixture designs are allowed by the lamps compact size, while the very short arc provides a high perceived brightness and high beam intensity.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050

### Product data

General information	
Base	PGJX28 [ PGJX28]
Operating Position	Universal [ Universal]
Main Application	Entertainment
Life to 50% Failures (Nom)	750 h
System Description	MiniFastFit

Light technical	
Color Code	- [ Not Specified]
Initial lumen (Min)	23400 lm
Initial lumen (Nom)	26000 lm
Chromaticity Coordinate X (Nom)	310
Chromaticity Coordinate Y (Nom)	320
Correlated Color Temperature (Nom)	6700 K
Luminous Efficacy (rated) (Nom)	65 lm/W

## MSR Gold™ MiniFastFit (Touring/Stage)

Color Rendering Index (Nom)	60
-----------------------------	----

### Operating and electrical

Power (Rated) (Nom)	400 W
Lamp Current (Nom)	7.2 A
Ignition Supply Voltage (Min)	198 V

### Controls and dimming

Dimmable	Yes
----------	-----

### Mechanical and housing

Cap-Base Information	PGJX28
----------------------	--------

### Luminaire design requirements


Bulb Temperature (Max)	1742 °F
------------------------	---------

Pinch Temperature (Max)	932 °F
-------------------------	--------

### Product data

Order product name	MSR Gold™ 400 MiniFastFit 1CT/16
EAN/UPC - Product	8718291158288
Order code	248963
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	16
Material Nr. (12NC)	928194005114
Copy Net Weight (Piece)	0.117 lb

## Dimensional drawing



MSR Gold™ 400 MiniFastFit 1CT/16

Product	D (max)	O	L (min)	L (max)	L (max)	C (max)	F (max)	F (min)	F (min)
MSR Gold™ 400 MiniFastFit 1CT/16	15/16 in	1/8 in	2-3/16 in	2-1/4 in	2-1/4 in	4-3/8 in	1-7/16 in	1-7/16 in	1-7/16 in

