



MSR Gold™ MiniFastFit (Touring/ Stage)

MSR Gold™ 700/2 MiniFastFit 1CT/4

Thanks to the specially designed lamp base, the MSR Gold™ MiniFastFit takes just seconds to replace, to help ensure non-stop clubbing entertainment. In addition, the innovative gold plated pins ensure excellent current transfer to prolong lamp and lamp holder lifetimes and thereby reduce lamp replacement costs. Easy handling and small compact fixture designs are allowed by the lamps compact size, while the very short arc provides a high perceived brightness and high beam intensity.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General information		Light technical	
Base	PGJX28 [PGJX28]	Color Code	2
Operating Position	Universal [Universal]	Initial lumen (Min)	44000 lm
Main Application	Entertainment	Initial lumen (Nom)	47000 lm
Life to 50% Failures (Nom)	750 h	Chromaticity Coordinate X (Nom)	300
System Description	MiniFastFit	Chromaticity Coordinate Y (Nom)	324
		Correlated Color Temperature (Nom)	7200 K
		Luminous Efficacy (rated) (Nom)	69 lm/W

MSR Gold™ MiniFastFit (Touring/Stage)

Color Rendering Index (Nom)	75
-----------------------------	----

Operating and electrical

Power (Rated) (Nom)	700 W
Lamp Current (Nom)	10.2 A
Ignition Supply Voltage (Min)	198 V

Controls and dimming

Dimmable	Yes
----------	-----

Mechanical and housing

Cap-Base Information	PGJX28
----------------------	--------

Luminaire design requirements


Bulb Temperature (Max)	1742 °F
------------------------	---------

Pinch Temperature (Max)	932 °F
-------------------------	--------

Product data

Order product name	MSR Gold™ 700/2 MiniFastFit 1CT/4
EAN/UPC - Product	8718291221173
Order code	286922
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	928199905115
Copy Net Weight (Piece)	0.115 lb


Dimensional drawing




MSR Gold™ 700/2 MiniFastFit 1CT/4

Product	D (max)	O	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSR Gold™ 700/2 MiniFastFit 1CT/4	15/16 in	3/16 in	2-3/16 in	2-1/4 in	2-1/4 in	4-7/16 in	1-7/16 in	1-7/16 in	1-7/16 in

Photometric data



XDPB_XDMSR_0004-Spectral power distribution B/W



MSR Gold™ MiniFastFit (Touring/Stage)

