



Ceramalux Instant Restrike

C400S51/2 12PK

Dual arc-tube delivers 40,000 hour rated average life as compared to 24,000 hour rated average life for standards HPS lamps. Ideal for industrial applications, warehouses, post top applications and parking lots.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Cap-Base	E39 [Single Contact Mogul Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]

Light Technical	
Chromaticity Coordinate X (Nom)	515
Chromaticity Coordinate Y (Nom)	418
Correlated Color Temperature (Nom)	2100 K
Luminous Efficacy (Rated) (Min)	112.5 lm/W
Luminous Efficacy (rated) (Nom)	125 lm/W
Color rendering index (CRI)	21

Operating and Electrical	
Power Consumption	401.5 W
Lamp Current (Nom)	4.6 A
Voltage (Nom)	100 V

Voltage (Nom)	100 V
---------------	-------

Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Hard Glass
Bulb Shape	ED18

Approval and Application	
Mercury (Hg) Content (Nom)	47 mg


Product Data	
Order product name	37688-9 400W C400S51/2 Dual Arc Hp Lamp
Order code	376889
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material number (12NC)	928601145401
Full product name	C400S51/2 12PK

Ceramalux Instant Restrike

EAN/UPC - Case

50046677376883

Dimensional drawing



Product	D	C (max)
37688-9 400W C400S51/2 Dual Arc Hp Lamp	2.25 inch	9.75 inch

