



Energy Advantage CDM Lamps with Allstart Technology

CDM330/U/O/4K EA 130V 6/1

Philips Energy Advantage CDM lamps with AllStart Technology is a high-efficiency protected “O” rated CDM lighting solution that provides energy savings without compromising light quality.

Warnings and Safety

- R "WARNING:These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data


General Information		Chromaticity Coordinate X (Nom)		Chromaticity Coordinate Y (Nom)	
Cap-Base	EX39 [Exclusionary Mogul Screw]		0.381		0.384
Operating Position	UNIVERSAL [Any or Universal (U)]				
Features	Energy Advantage AllStart				
Light Technical					
Color Code	940 [CCT of 4000K]				
Color Designation	4000 Kelvin				
Saturated Red (R9)	50				
		Operating and Electrical			
		Lamp Current (Nom)	3.02 A		
		Voltage (Nom)	130 V		

Energy Advantage CDM Lamps with Allstart Technology

Voltage (Nom)	130 V
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	ED37
Approval and Application	
Mercury (Hg) Content (Max)	50 mg
Product Data	
Order product name	Allstart Energy Adv 330W ED37 CL 1SL


Order code	232595
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material number (12NC)	928601165903
Full product name	CDM330/U/O/4K EA 130V 6/1
EAN/UPC - Case	50046677232592

Dimensional drawing



Product	D (max)	D	L (max)	L	C
Allstart Energy Adv 330W ED37 CL 1SL	118 mm	4.625 inch	184 mm	178 mm	11.5 inch


Photometric data




Spectral Power Distribution Colour - Allstart Energy Adv 330W ED37 CL 1SL

Energy Advantage CDM Lamps with Allstart Technology

Lifetime



Life Expectancy Diagram - Allstart Energy Adv 330W ED37 CL 1SL



Lumen Maintenance Diagram - Allstart Energy Adv 330W ED37 CL 1SL

