



CorePro LEDcapsule MV

CorePro LEDcapsuleMV 2.3-25W G9 827 D

This single-ended mains-voltage capsule for G9-base luminaires delivers directional light, making it a true alternative to halogen capsule lamps. It is particularly suitable for task lighting in shops, hotels and restaurants, and ideal for desk lamps and cabinet lighting. Compatible with existing fixtures with G9 holders and designed for retrofit replacement of halogen capsules, CorePro LEDcapsule delivers huge energy savings and minimizes maintenance costs, without any compromise on light quality.

Product data

General Information		Power (Rated) (Nom)	
Base	G9 [G9]		2.3 W
EU RoHS compliant	Yes	Lamp Current (Nom)	15 mA
Nominal Lifetime (Nom)	15000 h	Wattage Equivalent	25 W
Switching Cycle	50000X	Starting Time (Nom)	0.5 s
Technical Type	2.3-25W	Warm Up Time to 60% Light (Nom)	0.5 s
		Power Factor (Nom)	0.7
		Voltage (Nom)	220-240 V
Light Technical		Temperature	
Color Code	827 [CCT of 2700K]	T-Case Maximum (Nom)	82 °C
Initial lumen (Nom)	215 lm		
Color Designation	Warm White (WW)	Controls and Dimming	
Correlated Color Temperature (Nom)	2700 K	Dimmable	Yes
Luminous Efficacy (rated) (Nom)	93.48 lm/W		
Color Consistency	<6	Approval and Application	
Color Rendering Index (Nom)	80	Energy Efficiency Label (EEL)	A++
LLMF At End Of Nominal Lifetime (Nom)	70 %	Energy Saving Product	Yes
Operating and Electrical		Suitable For Accent Lighting	No
Input Frequency	50 to 60 Hz		

CorePro LEDcapsule MV

Energy Consumption kWh/1000 h	3 kWh
Product Data	
Order product name	CorePro LEDcapsuleMV 2.3-25W G9 827 D
EAN/UPC - Product	8718696578698
Order code	324533

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	929001232002
Net Weight (Piece)	0.012 kg



Dimensional drawing

D

Product	D	C
CorePro LEDcapsuleMV 2.3-25W G9 827 D	23 mm	51 mm


Capsule 230V 2.3W-25W 210lm 2700K G9 D

Photometric data



LED Lamps, CorePro LEDcapsuleMV D 2.3-25W G9 /827

LED Lamps, CorePro LEDcapsuleMV D 2.3-25W G9 /827



LED Lamps, CorePro LEDcapsuleMV D 2.3-25W G9 /827

CorePro LEDcapsule MV

