



T8

35T8/96-3500 IF FA8 10/1

The MasterClass InstantFit TLED is a great LED solution suitable for replacing T8 fluorescent lamps, using the existing ballast. MasterClass TLEDs feature a shatter-resistant polycarbonate construction. When maximum energy savings and long life are needed, Philips MasterClass TLEDs are the solution.

Product data


General information		Warm Up Time to 60% Light (Nom)	
Base	FA8 [FA8]		0.5 s
EU RoHS compliant	Yes	UL Type	Type A - works on ballast
Nominal Lifetime (Nom)	50000 h	Power Factor (Nom)	0.9
Switching Cycle	50000X	Voltage (Nom)	280-410 V
Light technical		Temperature	
Color Code	835 [CCT of 3500K]	T-Ambient (Max)	113 °F
Beam Angle (Nom)	180 °	T-Ambient (Min)	-4 °F
Initial lumen (Nom)	4000 lm	T-Storage (Max)	149 °F
Color Designation	White (WH)	T-Storage (Min)	-40 °F
Correlated Color Temperature (Nom)	3500 K	T-Case Maximum (Nom)	113 °F
Luminous Efficacy (rated) (Nom)	114.00 lm/W	Controls and dimming	
Color Consistency	<6	Dimmable	No
Color Rendering Index (Nom)	82	Mechanical and housing	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Finish	Frosted
Operating and electrical		Bulb Material	Plastic
Input Frequency	50000-64000 Hz	Product Length	96 in
Power (Rated) (Nom)	35 W	Bulb Shape	Tube, double-ended
Lamp Current (Max)	260 mA	Approval and application	
Lamp Current (Min)	160 mA	Energy Saving Product	Yes
Wattage Equivalent	96 W		

T8

Approbation Marks	UL certificate
Energy Consumption kWh/1000 h	- kWh
Product data	
Order product name	35T8/96-3500 IF FA8 10/1
EAN/UPC - Product	046677472573
Order code	469247

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001307804
Copy Net Weight (Piece)	1.19 lb
Model Number	9290013078



Dimensional drawing



35T8/96-3500 IF FA8 10/1

Product	D	A1	A2	A3
35T8/96-3500 IF FA8 10/1	1-1/8 in	93-3/16 in	93-9/16 in	93-7/8 in


Photometric data



General Lighting Fixture

TLED Ess 35W FA8 835 4000lm T8



TLED Ess 35W FA8 835 4000lm T8



TLED Ess 35W FA8 835 4000lm T8

T8

Lifetime



TLED Ess 35W FA8 T8 IF

TLED Ess 35W FA8 T8 IF

