



PL-C/T

8.5PL-C/T/COR/26H-827/IF8/P/4P/DIM 10/1

Philips PLED 4-pin & 2-pin lamps are an affordable LED solution to replace compact fluorescent lamps. The product provides a natural lighting effect for use in many lighting applications, and provides instant energy savings, making them an environmentally-friendly solution. Available as replacements for 13W, 26W and 32W compact fluorescent lamps.

Product data


| General information | | Power (Rated) (Nom) | |
|---------------------------------------|---------------------|---------------------------------|---------------------------|
| Base | G24Q [G24q] | | 8.5 W |
| EU RoHS compliant | Yes | Lamp Current (Max) | 550 mA |
| Main Application | Industrial | Lamp Current (Min) | 150 mA |
| Nominal Lifetime (Nom) | 50000 h | Wattage Equivalent | 26 W |
| Switching Cycle | 50000X | Starting Time (Nom) | 0.5 s |
| Technical Type | 8.5-26W | Warm Up Time to 60% Light (Nom) | 0.5 s |
| | | UL Type | Type A - works on ballast |
| | | Power Factor (Nom) | 0.9 |
| | | Voltage (Nom) | 120 V |
| Light technical | | Temperature | |
| Color Code | 827 [CCT of 2700K] | T-Ambient (Max) | 113 °F |
| Beam Angle (Nom) | 120 ° | T-Ambient (Min) | -4 °F |
| Initial lumen (Nom) | 850 lm | T-Storage (Max) | 149 °F |
| Luminous Flux (Rated) (Nom) | 850 lm | T-Storage (Min) | -40 °F |
| Color Designation | Warm White (WW) | T-Case Maximum (Nom) | 140 °F |
| Correlated Color Temperature (Nom) | 2700 K | | |
| Luminous Efficacy (rated) (Nom) | 100.00 lm/W | Controls and dimming | |
| Color Consistency | <6 | Dimmable | Yes |
| Color Rendering Index (Nom) | 82 | | |
| LLMF At End Of Nominal Lifetime (Nom) | 70 % | Mechanical and housing | |
| | | Bulb Finish | Frosted |
| Operating and electrical | | | |
| Input Frequency | 20000-100000 Hz | | |

PL-C/T

| | |
|--------------------------------------|---|
| Bulb Material | Plastic |
| Product Length | 8 in |
| Bulb Shape | Tube, single-ended |
| Approval and application | |
| Energy Saving Product | Yes |
| Approbation Marks | RoHS compliance UL certificate KEMA Keur certificate DLC compliance |
| Energy Consumption kWh/1000 h | - kWh |
| Energy Certifications | DLC Standard |

| | |
|--|---|
| Product data | |
| Order product name | 8.5PL-C/T/COR/26H-827/IF8/P/4P/DIM 10/1 |
| EAN/UPC - Product | 046677458362 |
| Order code | 458364 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 10 |
| Material Nr. (12NC) | 929001388004 |
| Copy Net Weight (Piece) | 0.181 lb |
| Model Number | 9290013880 |



Dimensional drawing



8.5PL-C/T/COR/26H-827/IF8/P/4P/DIM 10/1

| Product | D1 | D2 | A1 | A2 | A3 |
|---|------|----------|-----------|------------|-----------|
| 8.5PL-C/T/COR/ 26H-827/IF8/P/4P/DIM 10/1 | 1 in | 1-1/8 in | 5-1/16 in | 5-13/16 in | 6-7/16 in |


Photometric data



LEDtube PLC 100mm 9W G24Q GX24Q 827 850lm


LEDtube PLC 100mm 9W G24Q GX24Q 827 850lm

Photometric data




LEDtube PLC 100mm 9W G24Q GX24Q 827 850lm


Lifetime




LEDtube PLC 100mm 9W G24Q GX24Q 827 850lm



LEDtube PLC 100mm 9W G24Q GX24Q 827 850lm




LEDtube PLC 100mm 9W G24Q GX24Q 827 850lm



LEDtube PLC 100mm 9W G24Q GX24Q 827 850lm

PL-C/T

Lifetime



LEDtube PLC 100mm 9W G24Q GX24Q 827 850lm

