



PL-C/T

12PL-C/T/COR/32V-840/IF15/P/4P/DIM 10/1

Philips PLED 4-pin & 2-pin lamps are an affordable LED solution to replace compact fluorescent lamps. The product provides a natural lighting effect for use in many lighting applications, and provides instant energy savings, making them an environmentally-friendly solution. Available as replacements for 13W, 26W and 32W compact fluorescent lamps.

Product data


General Information		Power (Rated) (Nom)	
Base	GX24q	Power (Rated) (Nom)	12 W
EU RoHS compliant	Yes	Lamp Current (Max)	500 mA
Main Application	Industrial	Lamp Current (Min)	150 mA
Nominal Lifetime (Nom)	50000 h	Wattage Equivalent	32 W
Switching Cycle	50000X	Starting Time (Nom)	0.5 s
Technical Type	12-32W	Warm Up Time to 60% Light (Nom)	0.5 s
Light Technical		UL Type	Type A - works on ballast
Color Code	841 [CCT of 4100K (841)]	Power Factor (Nom)	0.9
Beam Angle (Nom)	120 °	Voltage (Nom)	25-55 V
Initial lumen (Nom)	1500 lm	Temperature	
Luminous Flux (Rated) (Nom)	1500 lm	T-Ambient (Max)	45 °C
Color Designation	Cool White (CW)	T-Ambient (Min)	-20 °C
Correlated Color Temperature (Nom)	4000 K	T-Storage (Max)	65 °C
Luminous Efficacy (rated) (Nom)	125.00 lm/W	T-Storage (Min)	-40 °C
Color Consistency	<6	T-Case Maximum (Nom)	25 °C
Color Rendering Index (Nom)	82	Controls and Dimming	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Dimmable	Yes
Operating and Electrical		Mechanical and Housing	
Input Frequency	20000-100000 Hz	Bulb Finish	Frosted

PL-C/T

Bulb Material	Plastic
Product Length	4 in
Bulb Shape	Tube, single-ended
Approval and Application	
Energy Saving Product	Yes
Approbation Marks	RoHS compliance UL certificate KEMA Keur certificate DLC compliance
Energy Consumption kWh/1000 h	- kWh
Energy Certifications	DLC Standard

Product Data	
Order product name	12PL-C/T/COR/32V-840/IF15/P/4P/DIM 10/1
EAN/UPC - Product	046677476137
Order code	476135
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001820404
Net Weight (Piece)	0.091 kg
Model Number	9290018204


Dimensional drawing




PLED 120V 12-32W 1500lm 4000K G24/Gx24

Product	D1	D2	A1	A2	A3
12PL-C/T/COR/32V-840/IF15/P/4P/DIM 10/1	24.3 mm	29 mm	99.9 mm	109.9 mm	125.5 mm

Photometric data




LEDtube PLC/T 12W G24Q 840 32V DIM



LEDtube PLC/T 12W G24Q 840 32V DIM


PL-C/T

Photometric data




LEDtube PLC/T 12W G24Q 827 32V DIM


Lifetime




LEDtube PLC/T 12W G24Q 827-840 32H-32V DIM



LEDtube PLC/T 12W G24Q 827-840 32H-32V DIM




LEDtube PLC/T 12W G24Q 827-840 32H-32V DIM



LEDtube PLC/T 12W G24Q 827-840 32H-32V DIM

PL-C/T

Lifetime



LEDtube PLC/T 12W G24Q 827-840 32V DIM

