



LED Specialty Lamps

3.6T3/PER/830/ND/G9/120V 6/3BC

Philips speciality LED lamps are the smart alternative to standard incandescent. Their unique lamp design provides form factors to fit in standard applications with incredible energy savings.

Product data

General information	
Base	G9 [G9]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	15000 h
Switching Cycle	50000X
Technical Type	3.6-40W

Light technical	
Color Code	830 [CCT of 3000K]
Initial lumen (Nom)	370 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	102.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and electrical	
Input Frequency	60 Hz
Power (Rated) (Nom)	3.6 W
Lamp Current (Nom)	60 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s

Power Factor (Nom)	0.5
Voltage (Nom)	120 V

Temperature	
T-Case Maximum (Nom)	78 °C

Controls and dimming	
Dimmable	No


Mechanical and housing	
Bulb Shape	Capsule

Approval and application	
Suitable For Accent Lighting	No

Product data	
Order product name	3.6T3/PER/830/ND/G9/120V 6/3BC
EAN/UPC - Product	50046677534269
Order code	534263
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929001840835
Net Weight (Piece)	0.007 kg

LED Specialty Lamps


Dimensional drawing




3.6T3/PER/830/ND/G9/120V 6/3BC

Product	D	C
3.6T3/PER/830/ND/G9/120V 6/3BC	17 mm	51.5 mm

Photometric data




CalcLux Photometrics 4.3 Philips Lighting B.V. Page 12



LEDcapsule 3,6W G9


LEDcapsule 3,6W G9 830



LEDcapsule 3,6W G9 830

LED Specialty Lamps

Lifetime



15K LED

15K LMP

