



TrueForce High Lumen PAR

25.5PAR30L/PER/830/F25/ND/120-277V 6/1FB

Philips LED TrueForce PAR high lumen lamps are the perfect transition from CDM lamps to LED.

Product data

General information		Wattage Equivalent	
Base	E26 [Single Contact Medium Screw]	Wattage Equivalent	75 W
EU RoHS compliant	Yes	Starting Time (Nom)	0.5 s
Nominal Lifetime (Nom)	25000 h	Warm Up Time to 60% Light (Nom)	0.5 s
Switching Cycle	50000	Power Factor (Nom)	0.8
Technical Type	25.5-75W	Voltage (Nom)	120-277 V
Light technical		Temperature	
Color Code	830 [CCT of 3000K]	T-Case Maximum (Nom)	203 °F
Beam Angle (Nom)	25 °	Controls and dimming	
Initial lumen (Nom)	2500 lm	Dimmable	No
Luminous Intensity (Nom)	11500 cd	Mechanical and housing	
Color Designation	White (WH)	Bulb Finish	Clear
Correlated Color Temperature (Nom)	3000 K	Bulb Material	Aluminum
Luminous Efficacy (rated) (Nom)	98.00 lm/W	Bulb Shape	PAR30L [PAR 3.75 inch/95mm Long]
Color Consistency	<4	Approval and application	
Color Rendering Index (Nom)	80	Suitable For Accent Lighting	Yes
LLMF At End Of Nominal Lifetime (Nom)	70 %	Energy Consumption kWh/1000 h	- kWh
Operating and electrical		Energy Certifications	Energy Star
Input Frequency	50 to 60 Hz		
Power (Rated) (Nom)	25.5 W		


TrueForce High Lumen PAR

Product data

Order product name	25.5PAR30L/PER/830/F25/ND/120-277V 6/1FB
EAN/UPC - Product	046677534653
Order code	534651
Numerator - Quantity Per Pack	1

Numerator - Packs per outer box	6
Material Nr. (12NC)	929001917104
Net Weight (Piece)	0.628 lb



Dimensional drawing



25.5PAR30L/PER/830/F25/ND/120-277V 6/1FB


Product	D	C
25.5PAR30L/PER/830/F25/ND/120-277V 6/1FB	3-13/16 in	4-11/16 in

Photometric data



LEDspot PAR30 1FB



LEDspot 25,5 PAR30L 830 F25



LEDspot 25,5 PAR30L 830 F25

TrueForce High Lumen PAR

Lifetime



LEDspot PAR30 1FB

LEDspot PAR30 1FB

