



TrueForce High Lumen PAR

25.5PAR30L/PER/930/F25/ND/120-277V 6/1FB

Philips LED TrueForce PAR high lumen lamps are the perfect transition from CDM lamps to LED.

Product data


General Information		Wattage Equivalent	
Base	E26 [Single Contact Medium Screw]	Wattage Equivalent	75 W
EU RoHS compliant	Yes	Starting Time (Nom)	0.5 s
Nominal Lifetime (Nom)	25000 h	Warm Up Time to 60% Light (Nom)	0.5 s
Switching Cycle	50000X	Power Factor (Nom)	0.8
Technical Type	25.5-75W	Voltage (Nom)	120-277 V
Light Technical		Temperature	
Color Code	930 [CCT of 3000K]	T-Case Maximum (Nom)	95 °C
Beam Angle (Nom)	25 °	Controls and Dimming	
Initial lumen (Nom)	2150 lm	Dimmable	No
Luminous Intensity (Nom)	10000 cd	Mechanical and Housing	
Color Designation	White (WH)	Bulb Shape	PAR30L [PAR 3.75 inch/95mm Long]
Correlated Color Temperature (Nom)	3000 K	Approval and Application	
Luminous Efficacy (rated) (Nom)	84.00 lm/W	Suitable For Accent Lighting	Yes
Color Consistency	<4	Energy Consumption kWh/1000 h	- kWh
Color Rendering Index (Nom)	90	Product Data	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Order product name	25.5PAR30L/PER/930/F25/ND/120-277V 6/1FB
Operating and Electrical			
Input Frequency	50 to 60 Hz		
Power (Rated) (Nom)	25.5 W		

TrueForce High Lumen PAR

EAN/UPC - Product	046677534677
Order code	534677
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6

Material Nr. (12NC)	929001917304
Net Weight (Piece)	0.285 kg


Dimensional drawing




PAR30L 27.5-W 2000lm 25D 3000K E26 ND

Product	D	C
25.5PAR30L/PER/930/F25/ND/120-277V 6/1FB	96 mm	119 mm


Photometric data



LEDspot 25,5 PAR30L 930 F25



LEDspot PAR30 1FB





© 2021 Philips Lighting B.V. Page 11

LEDspot 25,5 PAR30L 930 F25

TrueForce High Lumen PAR

Lifetime



LEDspot PAR30 1FB

LEDspot PAR30 1FB

