



TrueForce High Lumen PAR

23PAR30s/PER/930/F25/ND/120V 6/1FB

Philips LED TrueForce PAR high lumen lamps are the perfect transition from CDM lamps to LED.

Product data

General information	
Base	E26 [Single Contact Medium Screw]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	25000 h
Switching Cycle	50000
Technical Type	23-75W

Light technical	
Color Code	930 [CCT of 3000K]
Beam Angle (Nom)	25°
Initial lumen (Nom)	1900 lm
Luminous Intensity (Nom)	9000 cd
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	82.00 lm/W
Color Consistency	<4
Color Rendering Index (Nom)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	23 W

Lamp Current (Nom)	206 mA
Wattage Equivalent	75 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.9
Voltage (Nom)	120 V

Temperature	
T-Case Maximum (Nom)	201.2 °F

Controls and dimming	
Dimmable	No

Mechanical and housing	
Bulb Finish	Clear
Bulb Material	Aluminum
Bulb Shape	PAR30S [PAR 3.75 inch/95mm Short]


Approval and application	
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	- kWh

TrueForce High Lumen PAR

Energy Certifications	Energy Star
Product data	
Order product name	23PAR30s/PER/930/F25/ND/120V 6/1FB
EAN/UPC - Product	046677534691
Order code	534693

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929001917504
Net Weight (Piece)	0.485 lb


Dimensional drawing




23PAR30s/PER/930/F25/ND/120V 6/1FB

Product	D	C
23PAR30s/PER/930/F25/ND/120V 6/1FB	3-13/16 in	3-3/4 in


Photometric data



LEDspot 23 PAR30L 930 F25





LEDspot PAR30 1FB



LEDspot 23 PAR30L 930 F25

TrueForce High Lumen PAR

Lifetime



LEDspot PAR30 1FB

LEDspot PAR30 1FB

