



# LED PAR20

## 8.5PAR20/PER/927/F25/DIM/EC/120V 6/1FB

Philips is driving the switch to energy-efficient solutions. Upgrade your track and accent lights with our small diameter reflectors for instant energy savings and unbeatable quality. Available in both Glass and Plastic casings, Philips LED Par20s are the ideal replacement for halogen.

### Product data

General Information	
Base	E26 [ Single Contact Medium Screw]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	25000 h
Switching Cycle	50000X
Technical Type	8.5-50W
Light Technical	
Color Code	927
Beam Angle (Nom)	25°
Initial lumen (Nom)	600 lm
Luminous Intensity (Nom)	2450 cd
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	70.00 lm/W
Color Consistency	<4
Color Rendering Index (Nom)	95
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	8.5 W
Lamp Current (Nom)	86 mA


Wattage Equivalent	50 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.8
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	86 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	PAR20 [ PAR 2.5 inch]
Approval and Application	
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	- kWh
Product Data	
Order product name	8.5PAR20/PER/927/F25/DIM/EC/120V 6/1FB
EAN/UPC - Product	046677535261
Order code	535260

# LED PAR20

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929001921804

Net Weight (Piece)	0.135 kg
--------------------	----------



## Dimensional drawing



PAR20 120V 9-50W 550lm 25D 2700K E26 D


Product	D	C
8.5PAR20/PER/927/F25/DIM/EC/120V 6/1FB	64 mm	83.5 mm

## Photometric data



LEDspot PAR20 E26 2700K 25D 550lm



LEDspot PAR20 E26 2700K



LEDspot PAR20 E26 2700K 25D

# LED PAR20

## Lifetime



LEDSpot PAR20 E26

LEDSpot PAR20 E26

