



LED Designer Deco

4.5T10/VIN/820/E26/CL/GL/DIM 4/1BC T20


Philips LED Designer Deco lamps allow you to maintain a warm, classic light or a modern, chic effect while providing longer life and energy savings

Product data

General Information	
Base	E26 [Single Contact Medium Screw]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	15000 h
Switching Cycle	20000X
Technical Type	4.5-40W
Light Technical	
Color Code	820 [CCT of 2000K]
Initial lumen (Nom)	300 lm
Color Designation	Flame
Correlated Color Temperature (Nom)	2000 K
Luminous Efficacy (rated) (Nom)	66.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	60 Hz
Power (Rated) (Nom)	4.5 W
Lamp Current (Nom)	40 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.7

Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	55 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Amber
Approval and Application	
Energy Efficiency Label (EEL)	Not applicable
Energy Consumption kWh/1000 h	- kWh
Product Data	
Order product name	4.5T10/VIN/820/E26/CL/GL/DIM 4/1BC T20
EAN/UPC - Product	046677537609
Order code	537605
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	929001951553
Net Weight (Piece)	0.042 kg


Dimensional drawing




Bulb T10 4.5-40W 300lm 2000K D Amber

Product	D	C
4.5T10/VIN/820/E26/CL/GL/DIM 4/1BC T20	29 mm	190 mm


Photometric data



LEDbulb 4,5W T10 E26 820 Amber





LEDbulb 4,5W T10 E26 820 Amber



LEDbulb T10 4,5W E26 820 Amber

Lifetime



15K LED

15K LMP

