



LED BR40

8.8BR40/PER/927-22/P/E26/WG 6/1FB T20

Philips BR40 LED lamps are the smart alternative to standard incandescent. The traditional lamp design can provide excellent dimming performance with spectacular energy savings. They provide the beautiful light and dependable performance you expect from LED at an economical price.

Product data


General Information	
Base	E26 [Single Contact Medium Screw]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	15000 h
Switching Cycle	50000X
Technical Type	8.8-65W
Light Technical	
Color Code	922-927 [CCT of 2200K-2700K]
Beam Angle (Nom)	90 °
Initial lumen (Nom)	800 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	- K
Luminous Efficacy (rated) (Nom)	90.00 lm/W
Color Consistency	<4
Color Rendering Index (Nom)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	60 Hz
Power (Rated) (Nom)	8.8 W
Lamp Current (Nom)	95 mA
Wattage Equivalent	65 W

Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.7
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	75 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	BR40 [BR40 (BR40)]
Approval and Application	
Energy Consumption kWh/1000 h	- kWh
Product Data	
Order product name	8.8BR40/PER/927-22/P/E26/WG 6/1FB T20
EAN/UPC - Product	046677457013
Order code	457010
Numerator - Quantity Per Pack	1

LED BR40

Numerator - Packs per outer box	6
Material Nr. (12NC)	929002009104
Net Weight (Piece)	0.165 kg


Dimensional drawing




BR40 120V 8.9-65W 800lm 2700-2200K E26 D

Product	D	C
8.8BR40/PER/927-22/P/E26/WG 6/1FB T20	125 mm	160 mm


Photometric data



LEDBulbs_BR40 120V 89-65W 800lm 2700-2200K E26 D



LEDBulbs_BR40 120V 89-65W 800lm 2700-2200K E26 D





© 2021 Philips Lighting B.V. Page 11

LEDBulbs_BR40 120V 89-65W 800lm 2700-2200K E26 D

LED BR40

Lifetime



LEDBulbs BR30 120V 19-120W 1200lm 2700K E26 D

LEDBulbs BR30 120V 19-120W 1200lm 2700K E26 D

