



# LED PAR30 S/L

## 9.4PAR30L/COR/930/F25/DIM/120V T20 6/1FB

Philips LED spots with a single optic beam, provide a clean beam that's free from shadows with beam angles from 15 and 40 degrees to suit every general lighting application.

### Product data

General information	
Base	E26 [ Single Contact Medium Screw]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	25000 h
Switching Cycle	50000X
Technical Type	9.4-75W
Light technical	
Color Code	930 [ CCT of 3000K]
Beam Angle (Nom)	25 °
Initial lumen (Nom)	850 lm
Luminous Intensity (Nom)	2910 cd
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	90.00 lm/W
Color Consistency	<4
Color Rendering Index (Nom)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	9.4 W
Lamp Current (Nom)	90 mA
Wattage Equivalent	75 W


Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.9
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	176 °F
Controls and dimming	
Dimmable	Yes
Mechanical and housing	
Bulb Finish	Clear
Bulb Material	Plastic
Bulb Shape	PAR30L [ PAR 3.75 inch/95mm Long]
Approval and application	
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	- kWh
Energy Certifications	Energy Star
Product data	
Order product name	9.4PAR30L/COR/930/F25/DIM/120V T20 6/1FB

# LED PAR30 S/L

EAN/UPC - Product	046677546960
Order code	546969
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6

Material Nr. (12NC)	929002045404
Copy Net Weight (Piece)	0.628 lb


## Dimensional drawing




9.4PAR30L/COR/930/F25/DIM/120V T20 6/1FB

Product	D	C
9.4PAR30L/COR/930/F25/DIM/120V T20 6/1FB	3-13/16 in	4-11/16 in


## Photometric data



LEDspots 9,4W PAR30L E26 930 25D



LEDspots 9,4W PAR30L E26 930 25D




© 2022 Philips Lighting B.V. Page 11

LEDspots 9,4W PAR30L E26 930 25D

# LED PAR30 S/L

## Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram

