



LED PAR30 S/L

9.4PAR30L/COR/930/F40/DIM/120V T20 6/1FB

Philips LED spots with a single optic beam, provide a clean beam that's free from shadows with beam angles from 15 and 40 degrees to suit every general lighting application.

Product data


| General Information | |
|---------------------------------------|------------------------------------|
| Base | E26 [Single Contact Medium Screw] |
| EU RoHS compliant | Yes |
| Nominal Lifetime (Nom) | 25000 h |
| Switching Cycle | 50000X |
| Technical Type | 9.4-75W |
| Light Technical | |
| Color Code | 930 [CCT of 3000K] |
| Beam Angle (Nom) | 40 ° |
| Initial lumen (Nom) | 850 lm |
| Luminous Intensity (Nom) | 1315 cd |
| Color Designation | White (WH) |
| Correlated Color Temperature (Nom) | 3000 K |
| Luminous Efficacy (rated) (Nom) | 90.00 lm/W |
| Color Consistency | <4 |
| Color Rendering Index (Nom) | 90 |
| LLMF At End Of Nominal Lifetime (Nom) | 70 % |
| Operating and Electrical | |
| Input Frequency | 50 to 60 Hz |
| Power (Rated) (Nom) | 9.4 W |
| Lamp Current (Nom) | 90 mA |
| Wattage Equivalent | 75 W |

| Starting Time (Nom) | 0.5 s |
|---------------------------------|--|
| Warm Up Time to 60% Light (Nom) | 0.5 s |
| Power Factor (Nom) | 0.9 |
| Voltage (Nom) | 120 V |
| Temperature | |
| T-Case Maximum (Nom) | 80 °C |
| Controls and Dimming | |
| Dimmable | Yes |
| Mechanical and Housing | |
| Bulb Shape | PAR30L [PAR 3.75 inch/95mm Long] |
| Approval and Application | |
| Suitable For Accent Lighting | Yes |
| Energy Consumption kWh/1000 h | - kWh |
| Product Data | |
| Order product name | 9.4PAR30L/COR/930/F40/DIM/120V T20 6/1FB |
| EAN/UPC - Product | 046677546977 |
| Order code | 546977 |
| Numerator - Quantity Per Pack | 1 |

LED PAR30 S/L

| | |
|---------------------------------|--------------|
| Numerator - Packs per outer box | 6 |
| Material Nr. (12NC) | 929002045504 |
| Net Weight (Piece) | 0.285 kg |


Dimensional drawing




JA8 PAR30L 9.4-75W 850lm 40D 3000K E26 D

| Product | D | C |
|--|-------|--------|
| 9.4PAR30L/COR/930/F40/DIM/120V T20 6/1FB | 97 mm | 119 mm |


Photometric data



LEDspots 9,4W PAR30L E26 930 40D



LEDspots 9,4W PAR30L E26 930 40D




© 2021 Philips Lighting B.V. Page 11

LEDspots 9,4W PAR30L E26 930 40D

LED PAR30 S/L

Lifetime



LEDspots LED 25K

LEDspots LMP 25K

