



LED PAR38

10PAR38/COR/930/F25/DIM/120V T20 6/1FB

Philips LED spots with a single optic beam, provide a clean beam that's free from shadows with beam angles from 15 and 40 degrees to suit every general lighting application.

Product data


| General Information | |
|---------------------------------------|------------------------------------|
| Base | E26 [Single Contact Medium Screw] |
| EU RoHS compliant | Yes |
| Nominal Lifetime (Nom) | 25000 h |
| Switching Cycle | 50000X |
| Technical Type | 10-90W |
| Light Technical | |
| Color Code | 930 [CCT of 3000K] |
| Beam Angle (Nom) | 25 ° |
| Initial lumen (Nom) | 900 lm |
| Luminous Intensity (Nom) | 3698 cd |
| Color Designation | White (WH) |
| Correlated Color Temperature (Nom) | 3000 K |
| Luminous Efficacy (rated) (Nom) | 90.00 lm/W |
| Color Consistency | <4 |
| Color Rendering Index (Nom) | 90 |
| LLMF At End Of Nominal Lifetime (Nom) | 70 % |
| Operating and Electrical | |
| Input Frequency | 50 to 60 Hz |
| Power (Rated) (Nom) | 10 W |
| Lamp Current (Nom) | 110 mA |
| Wattage Equivalent | 90 W |

| Starting Time (Nom) | 0.5 s |
|---------------------------------|----------------------------------------|
| Warm Up Time to 60% Light (Nom) | 0.5 s |
| Power Factor (Nom) | 0.9 |
| Voltage (Nom) | 120 V |
| Temperature | |
| T-Case Maximum (Nom) | 80 °C |
| Controls and Dimming | |
| Dimmable | Yes |
| Mechanical and Housing | |
| Bulb Shape | PAR38 [PAR 4.75 inch/121mm] |
| Approval and Application | |
| Suitable For Accent Lighting | Yes |
| Energy Consumption kWh/1000 h | - kWh |
| Product Data | |
| Order product name | 10PAR38/COR/930/F25/DIM/120V T20 6/1FB |
| EAN/UPC - Product | 046677551889 |
| Order code | 551887 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 6 |

LED PAR38

| | |
|---------------------|--------------|
| Material Nr. (12NC) | 929002238204 |
| Net Weight (Piece) | 0.385 kg |


Dimensional drawing




PAR38 120V 10-120W 900lm 25D 3000K E26 D

| Product | D | C |
|----------------------------------------|--------|--------|
| 10PAR38/COR/930/F25/DIM/120V T20 6/1FB | 125 mm | 131 mm |


Photometric data



LEDspots 10W PAR38 E26 930 25D



LEDspots 10W PAR38 E26 930 25D



DocId:34000000-01 Page 1/1


LEDspots 10W PAR38 E26 930 25D

LED PAR38

Lifetime



LEDspots LED 25K



LEDspots LMP 25K

