



LED A15

3.3A15/VIN/820/E26/CL/GL/DIM 4/FBHT20

Philips A15 LED Lamps offer energy saving ambience with an elegant effect. Their unique design provides light in all directions, giving lighting designers a long life alternative to standard incandescent sources.

Product data

General information	
Base	E26 [Single Contact Medium Screw]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	15000 h
Switching Cycle	20000X
Technical Type	3.3-25W

Light technical	
Color Code	820 [CCT of 2000K]
Initial lumen (Nom)	200 lm
Color Designation	Flame
Correlated Color Temperature (Nom)	2000 K
Luminous Efficacy (rated) (Nom)	60.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and electrical	
Input Frequency	60 Hz
Power (Rated) (Nom)	3.3 W
Lamp Current (Nom)	40 mA
Wattage Equivalent	25 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s

Power Factor (Nom)	0.7
Voltage (Nom)	120 V

Temperature	
T-Case Maximum (Nom)	50 °C

Controls and dimming	
Dimmable	Yes


Mechanical and housing	
Bulb Finish	Transparent Amber
Bulb Shape	A15 [A 15mm]

Approval and application	
Energy Consumption kWh/1000 h	- kWh

Product data	
Order product name	3.3A15/VIN/820/E26/CL/GL/DIM 4/FBHT20
EAN/UPC - Product	046677556556
Order code	556555
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	929002260203
Net Weight (Piece)	0.018 kg

LED A15


Dimensional drawing




3.3A15/VIN/820/E26/CL/GL/DIM 4/FBHT20

Product	D	C
3.3A15/VIN/820/E26/CL/GL/DIM 4/FBHT20	47 mm	84 mm


Photometric data



LEDbulb A15 3,3W E26 820 TA



LEDbulb 3,3W A15 E26 820 TA





General Uniform Lightness

LEDbulb 3,3W A15 E26 820 TA

LED A15

Lifetime



15K LED

15K LMP

