

LED Designer Deco

8.8ST19/PER/950/CL/G/E26/DIM 1PF T20


Philips LED Designer Deco lamps allow you to maintain a warm, classic light or a modern, chic effect while providing longer life and energy savings

Product data

General information	
Base	E26 [Single Contact Medium Screw]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	15000 h
Switching Cycle	20000X
Technical Type	8.8-60W
Light technical	
Color Code	950 [CCT of 5000K]
Beam Angle (Nom)	280 °
Initial lumen (Nom)	800 lm
Color Designation	Daylight
Correlated Color Temperature (Nom)	5000 K
Luminous Efficacy (rated) (Nom)	90.00 lm/W
Color Consistency	<4
Color Rendering Index (Nom)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and electrical	
Input Frequency	60 Hz
Power (Rated) (Nom)	8.8 W
Lamp Current (Nom)	95 mA
Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s

Power Factor (Nom)	0.7
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	60 °C
Controls and dimming	
Dimmable	Yes
Mechanical and housing	
Bulb Finish	Clear
Bulb Shape	ST19
Approval and application	
Energy Consumption kWh/1000 h	- kWh
Product data	
Order product name	8.8ST19/PER/950/CL/G/E26/DIM 1PF T20
EAN/UPC - Product	046677556549
Order code	556548
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	929002296103
Net Weight (Piece)	0.030 kg


Dimensional drawing




8.8ST19/PER/950/CL/G/E26/DIM 1PF T20

Product	D	C
8.8ST19/PER/950/CL/G/E26/DIM 1PF T20	64 mm	143 mm


Photometric data



LEDbulb 8,8W ST19 E26 950 CL



LEDbulb ST19 8,8W E26 950 CL





General Uniform Lightness Page 1/1

LEDbulb 8,8W ST19 E26 950 CL

LED Designer Deco

Lifetime



15K LED

15K LMP

