



LED Dusk to Dawn

8.8A19/AMB/927/ND D2D 4/1FB T20

Philips Dusk to Dawn A19 lamp is equipped with a built in light sensor that turns the lights on automatically when the sun goes down and turns the light off when the sun rises.

Product data

General information	
Base	E26 [Single Contact Medium Screw]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	15000 h
Switching Cycle	50000X
Technical Type	8.8-60W

Light technical	
Color Code	927 [CCT of 2700K]
Beam Angle (Nom)	220 °
Initial lumen (Nom)	800 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	90.00 lm/W
Color Consistency	<4
Color Rendering Index (Nom)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and electrical	
Input Frequency	60 Hz
Power (Rated) (Nom)	8.8 W
Lamp Current (Nom)	74 mA
Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s

Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.7
Voltage (Nom)	120 V

Temperature	
T-Case Maximum (Nom)	95 °C


Controls and dimming	
Dimmable	No

Mechanical and housing	
Bulb Finish	Frosted
Bulb Shape	A19 (A19)

Product data	
Order product name	8.8A19/AMB/927/ND D2D 4/1FB T20
EAN/UPC - Product	046677557720
Order code	557728
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	929002333603
Net Weight (Piece)	0.060 kg

LED Dusk to Dawn



Dimensional drawing



8.8A19/AMB/927/ND D2D 4/1FB T20

Product	D	C
8.8A19/AMB/927/ND D2D 4/1FB T20	61.5 mm	109.8 mm


Photometric data



OSRAM Powerline LED Philips Lighting NV Page 1/1

LEDbulb 8,8W A19 E26 927 FR

LEDbulb 8,8W A19 E26 927 FR



LEDbulb A19 E26 800lm FR

LED Dusk to Dawn

Lifetime



15K LED

15K LMP

