



# LED BR40

## 20BR40/PER/927-22/E26/WG/HO 4/1FB T20

Philips BR40 LED lamps are the smart alternative to standard incandescent. The traditional lamp design can provide excellent dimming performance with spectacular energy savings. They provide the beautiful light and dependable performance you expect from LED at an economical price.


### Product data

General information	
Base	E26 [ Single Contact Medium Screw]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	15000 h
Switching Cycle	50000X
Technical Type	20-150W
Light technical	
Color Code	927-922 [ CCT of 2700K-2200K]
Beam Angle (Nom)	110 °
Initial lumen (Nom)	2175 lm
Color Designation	Warm Glow(WG)
Correlated Color Temperature (Nom)	2700 2200 K
Luminous Efficacy (rated) (Nom)	108.00 lm/W
Color Consistency	<4
Color Rendering Index (Nom)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and electrical	
Input Frequency	60 Hz
Power (Rated) (Nom)	20 W
Lamp Current (Nom)	180 mA
Wattage Equivalent	150 W

Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.7
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	85 °C
Controls and dimming	
Dimmable	Yes
Mechanical and housing	
Bulb Finish	Frosted
Bulb Shape	BR40
Product data	
Order product name	20BR40/PER/927-22/E26/WG/HO 4/1FB T20
EAN/UPC - Product	046677558048
Order code	558049
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	929002351203
Net Weight (Piece)	0.182 kg

# LED BR40


## Dimensional drawing




20BR40/PER/927-22/E26/WG/HO 4/1FB T20

Product	D	C
20BR40/PER/927-22/E26/WG/HO 4/1FB T20	123 mm	158 mm


## Photometric data



LEDbulb 20W BR40 E26 927 922 FR




LEDbulb BR30 E26 1400lm FR



LEDbulb 20W BR40 E26 927 922 FR

# LED BR40

## Lifetime



15K LED

15K LMP

