



# LED Wallpack Retrofits

## 20WP/LED/830/ND E26 G2 BB 6/1

Philips LED HID replacement lamps are perfect LED replacement for a variety of outdoor applications. High intensity illumination, which means you get added visibility for applications like streets, public areas, and much more for a fraction of the energy used by conventional HID.

### Product data

General Information	
Base	E26 [ Single Contact Medium Screw]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	50000 h
Switching Cycle	50000X
Technical Type	20-70-100W
Light Technical	
Color Code	830 [ CCT of 3000K]
Initial lumen (Nom)	2800 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	140.00 lm/W
Color Consistency	ANSI 3000K quadrangle
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	20 W

Lamp Current (Nom)	222 mA
Starting Time (Nom)	1 s
Warm Up Time to 60% Light (Nom)	1 s
Power Factor (Nom)	0.9
Voltage (Nom)	100-277 V
Temperature	
T-Case Maximum (Nom)	60 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear
Approval and Application	
Energy Efficiency Label (EEL)	A++
Energy Consumption kWh/1000 h	20 kWh


# LED Wallpack Retrofits

## Product Data

Order product name	20WP/LED/830/ND E26 G2 BB 6/1
EAN/UPC - Product	046677559908
Order code	559906
Numerator - Quantity Per Pack	1

Numerator - Packs per outer box	6
Material Nr. (12NC)	929002397904
Net Weight (Piece)	0.486 kg


## Dimensional drawing



Wallpack LED 20W E26 830 CL


Product	D	C
20WP/LED/830/ND E26 G2 BB 6/1	92 mm	135 mm

## Photometric data




General Information E1 - Photometry E1 Page 117

LEDTForce 20W WallPack E26 830





LEDTForce 20W WallPack E26 830



LEDTForce WallPack

# LED Wallpack Retrofits

## Lifetime



50K

50K

