



LED Wallpack Retrofits

20WP/LED/840/ND E26 G2 BB 6/1

Philips LED HID replacement lamps are perfect LED replacement for a variety of outdoor applications. High intensity illumination, which means you get added visibility for applications like streets, public areas, and much more for a fraction of the energy used by conventional HID.

Product data

General Information	
Base	E26 [Single Contact Medium Screw]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	50000 h
Switching Cycle	50000X
Technical Type	20-70-100W
Light Technical	
Color Code	841 [CCT of 4100K (841)]
Initial lumen (Nom)	2900 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	145.00 lm/W
Color Consistency	ANSI 4000K quadrangle
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	20 W

Lamp Current (Nom)	222 mA
Starting Time (Nom)	1 s
Warm Up Time to 60% Light (Nom)	1 s
Power Factor (Nom)	0.9
Voltage (Nom)	100-277 V
Temperature	
T-Case Maximum (Nom)	60 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear
Approval and Application	
Energy Efficiency Label (EEL)	A++
Energy Consumption kWh/1000 h	20 kWh


LED Wallpack Retrofits

Product Data

Order product name	20WP/LED/840/ND E26 G2 BB 6/1
EAN/UPC - Product	046677559915
Order code	559914
Numerator - Quantity Per Pack	1

Numerator - Packs per outer box	6
Material Nr. (12NC)	929002398004
Net Weight (Piece)	0.486 kg


Dimensional drawing



Wallpack LED 20W E26 840 CL


Product	D	C
20WP/LED/840/ND E26 G2 BB 6/1	92 mm	135 mm

Photometric data




General Uniform Lighting
1 - SIMPLE LED WALL PACKING
General Illumination E1
Photometry E1
Page 11

LEDForce 20W WallPack E26 840





LEDForce WallPack



LEDForce 20W WallPack E26 840

LED Wallpack Retrofits

Lifetime



50K

50K

