



OccuSwitch Classic Wallbox

Wall switch sensor, multi-tech dual switch, 120/277VAC

Wall switch sensor, multi-tech dual switch, 120/277VAC

OccuSwitch wall switch and low voltage occupancy sensors automatically turn lights off when a work space is unoccupied, saving energy and creating a more sustainable work environment. The ceiling mounted sensor communicates with a network of wall switches and dimmers. Using a combination of ultrasonic and passive infrared (PIR) technology, the sensor recognizes room occupancy or vacancy for maximum performance and energy savings.

Product data

General Information	
Downlight Type	Controls
Mounting	Wall Surface
Operating and Electrical	
Voltages	120/277 V
Mechanical and Housing	
Shape	Rectangular

Product Data	
Order product name	Wall switch sensor, multi-tech dual switch, 120/277VAC
Order code	LRS2225
Material Nr. (12NC)	PLC00000059
Commercial Code	LRS2225
Catalog Number Description	Wall switch sensor, multi-tech dual switch, 120/277VAC