



OccuSwitch Classic Power Packs

Power pack, 120-230-277VAC

Power pack, 120-230-277VAC

OccuSwitch wall switch and low voltage occupancy sensors automatically turn lights off when a work space is unoccupied, saving energy and creating a more sustainable work environment. The ceiling mounted sensor communicates with a network of wall switches and dimmers. Using a combination of ultrasonic and passive infrared (PIR) technology, the sensor recognizes room occupancy or vacancy for maximum performance and energy savings.

Product data

General Information	
Downlight Type	Controls
Operating and Electrical	
Voltages	120/277 V
Mechanical and Housing	
Shape	Rectangular

Product Data	
Order product name	Power pack, 120-230-277VAC
Order code	LCA2285
Material Nr. (12NC)	PLC00000068
Commercial Code	LCA2285
Catalog Number Description	Power pack, 120-230-277VAC