

# PHILIPS

LED lamps

CorePro Dimmable  
MR16 Lamps



## Affordable, high-quality lamps, **perfect for accent lighting**

**The CorePro LED MR16** lamps are an affordable and ideal solution for spot and general retrofit lighting applications in the hospitality and retail industries.

These lamps have a new look and feel with a single optics lens, while providing a crisp and uniform beam.

### Easy to experience

- 25,000-hr life<sup>1</sup>
- Suitable for use in enclosed fixtures<sup>2</sup>
- “Perfect fit” mechanical design fits most MR16 fixtures

1. LED lifetime means the length of time (in hours) until half of the LED light sources maintain at least 70% of their initial lumen output (B50, L70). Lamps rated 50,000 hours is for bare lamp without fixture.

2. See Technical Application Guide for complete details. All lamps include an over temperature protection (OTP) feature that systematically reduces the lamp power and consequently its internal temperature should it be subjected to abnormally high ambient temperature conditions.

# CorePro dimmable MR16 lamps



Ordering, electrical and technical data (Subject to change without notice)

Product Number	Model Number	Description	Watts (W)	Beam Angle	MBCP	Lumens (lm)	Volts (V)	Base	CRI (min)	Lifetime <sup>1</sup> (hrs)	CCT (K)	Dimmable
<b>CorePro MR16 50W replacement lamps</b>												
573865	929003076204	7MR16/LED/827/F25/DIM 12V 10/1FB	7	25	2400	515	12	GU5.3	80	25,000	2700	Yes
533125	929001880804	7.3MR16/LED/830/F25/DIM 12V 10/1FB	7.3	25	2500	515	12	GU5.3	80	25,000	3000	Yes
573881	929003076404	7MR16/LED/827/F35/DIM 12V 10/1FB	7	35	1350	515	12	GU5.3	80	25,000	2700	Yes
573899	929003076504	7MR16/LED/830/F35/DIM 12V 10/1FB	7	35	1350	515	12	GU5.3	80	25,000	3000	Yes
<b>CorePro MR16 75W replacement lamps</b>												
573907	929003072504	8MR16/LED/827/F25/DIM 12V 10/1FB	8	25	3100	600	12	GU5.3	80	25,000	2700	Yes
573915	929003072604	8MR16/LED/830/F25/DIM 12V 10/1FB	8	25	3250	620	12	GU5.3	80	25,000	3000	Yes
533521	929001881504	8.5MR16/LED/840/F25/DIM 12V 10/1FB	8.5	25	2900	621	12	GU5.3	–	25,000	4000	Yes
533182	929001881604	8.5MR16/LED/827/F35/DIM 12V 10/1FB	8.5	25	1500	621	12	GU5.3	80	25,000	2700	Yes
573949	929003072804	8MR16/LED/830/F35/DIM 12V 10/1FB	8	35	1700	620	12	GU5.3	80	25,000	3000	Yes
533331	9290018818-10	8.5MR16/LED/840/F35/DIM 12V 10/1FB	8.5	40	1500	621	12	GU5.3	80	25,000	4000	Yes

1. LED lifetime means the length of time (in hours) until half of the LED light sources maintain at least 70% of their initial lumen output (B50, L70). Lamps rated 50,000 hours is for bare lamp without fixture.

= Damp location = Suitable for enclosed fixtures = ENERGY STAR® qualified



© 2020 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

PLT-18136BN 06/21 philips.com/lighting



Signify North America Corporation  
200 Franklin Square Drive,  
Somerset, NJ 08873  
Telephone 855-486-2216

Signify Canada Ltd.  
281 Hillmount Road,  
Markham, ON, Canada L6C 2S3  
Telephone 800-668-9008

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.