

# PHILIPS

## LED

### GU10 and PAR20 lamps



---

## The optimal LED accent light in a **sleek design for a seamless look**

Philips is driving the switch to energy-efficient solutions. Upgrade your track and accent lights with our small diameter reflectors for instant energy savings and unbeatable quality. Featuring dimming with a warm glow effect (2700K only), Philips LEDs are the ideal replacement for halogen.

### Benefits

- Saves 86% energy when compared to a 50W halogen PAR20†
- GU10 options are T20 compliant and can be sold in California
- Long life lowers maintenance costs by reducing re-lamp frequency
- Will not fade colors, avoids inventory spoilage
- Contains no mercury

### Features

- Conventional look and feel
- Color warms when dimmed (2700K to 2200K)
- 25,000-hour rated average life for Energy Star® qualified lamps\*
- 3-year limited warranty depending upon operating hours‡

# Philips GU10 and PAR20 LED lamps

## Ordering, electrical and technical data (Subject to change without notice)

Product Number	12NC	Description	Watts	Replacement Watts	Lumens	Volts	CRI	LED Lifetime <sup>1,2</sup>	CCT	MC/CP <sup>3</sup>	MBCP <sup>2</sup> (Cd)	Dim <sup>4</sup>	Energy Star ID
<b>GU10 lamps</b>													
47156-5	929002055304	4GU10/LED/927-22/F35/G/WG/T20 10/1	4	50	380	120	90	25,000	2700-2200	MC	600	Y	2288364
46814-0	929002055504	4GU10/LED/930/F35/DIM/G/120V T20 10/1	4	50	380	120	90	25,000	3000	MC	600	Y	2296934
<b>PAR20 lamps (E26 – Medium base)</b>													
47111-0	9290013165	7PAR20/LED/F25/830/E26/GL/DIM 120V	7	50	500	120	80	25,000	3000	CP	1500	Y	2298258
47112-8	9290013167	7PAR20/LED/F25/840/E26/GL/DIM 120V	7	50	500	120	80	25,000	4000	CP	1500	Y	2298256
47114-4	9290013169	7PAR20/LED/F40/830/E26/GL/DIM 120V	7	50	500	120	80	25,000	3000	CP	1000	Y	2298257
47115-1	9290013170	7PAR20/LED/F40/840/E26/GL/DIM 120V	7	50	500	120	80	25,000	4000	CP	1000	Y	2298255
47110-2	9290013172	7PAR20/LED/F25/827-822/E26/GL/DIM 120V	7	50	500	120	80	25,000	2700-2200	CP	1500	Y	2300052
47113-6	9290013173	7PAR20/LED/F40/827-822/E26/GL/DIM 120V	7	50	500	120	80	25,000	2700-2200	CP	800	Y	2300054

## Energy saving solution

<b>Estimated lighting costs using a standard 50W PAR20 halide lamp</b>		
Present wattage	50	W
× Annual operating hours	4,000	hrs
=	200,000	Watt-Hours
÷ 1,000	200	kWh per year
× kWh rate of \$0.11	\$22.00	per year
× 100 lamps	\$2,200.00	annual energy cost per space
<b>Estimated lighting costs using a Philips 6W PAR20 LED replacement lamp</b>		
Present wattage	7	W
× Annual operating hours	4,000	hrs
=	28,000	Watt-Hours
÷ 1,000	28	kWh per year
× kWh rate of \$0.11	\$3.08	per year
× 100 lamps	\$308.00	annual energy cost per space
<b>Total estimated annual savings<sup>§</sup></b>	<b>\$1,892.00</b>	

§ Based on 100 lamps per space operating at 4,000 hours per year at 11¢/kWh. Cost depends on rates and use.

This example shows an application of 100 7W LED PAR20 replacement lamps operating 4,000 hours per year at a cost of \$0.11 per kWh. Replacing 100 standard 50W PAR20 halogen lamps with the Philips LED replacement lamps can provide significant energy cost savings of \$1,892.00 per year. Your actual savings may vary depending on the energy costs in your geographic location.

# Philips GU10 and PAR20 LED lamps

## Shipping data (Subject to change without notice)

Product Number	SKU UPC (0-46677)	Outer Bar Code (5-00-46677)	Case Qty.	Case Weight (lbs.)	Case Volume (cu.ft.)	Pallet Qty.	SKUs per Layer	Layers High	SKU Dimensions (L x W x H) (In.)	Case Dimensions (L x W x H) (In.)	Pallet Dimensions (L x W x H) (In.)
47156-5	47156-9	47156-4	10	1.52	0.081	5700	380	15	2.0 x 2.0 x 2.4	10.4 x 4.5 x 3.0	48.0 x 40.0 x 51.6
46814-0	46814-9	46814-4	10	1.52	0.081	5700	380	15	2.0 x 2.0 x 2.4	10.4 x 4.5 x 3.0	48.0 x 40.0 x 51.6
47111-0	46498-1	46498-6	6	38.55	0.12	2244	204	11	2.8 x 2.7 x 3.6	8.6 x 5.8 x 4.2	47.2 x 39.4 x 52.1
47112-8	46499-8	46499-3	6	38.55	0.12	2244	204	11	2.8 x 2.7 x 3.6	8.6 x 5.8 x 4.2	47.2 x 39.4 x 52.1
47114-4	46372-4	46372-9	6	38.55	0.12	2244	204	11	2.8 x 2.7 x 3.6	8.6 x 5.8 x 4.2	47.2 x 39.4 x 52.1
47115-1	46364-9	46364-4	6	38.55	0.12	2244	204	11	2.8 x 2.7 x 3.6	8.6 x 5.8 x 4.2	47.2 x 39.4 x 52.1
47110-2	46365-6	46365-1	6	38.55	0.12	2244	204	11	2.8 x 2.7 x 3.6	8.6 x 5.8 x 4.2	47.2 x 39.4 x 52.1
47113-6	46366-3	46366-8	6	38.55	0.12	2244	204	11	2.8 x 2.7 x 3.6	8.6 x 5.8 x 4.2	47.2 x 39.4 x 52.1

### WARNINGS AND CAUTIONS

- Suitable for use in damp locations.
- Can be used in enclosed luminaires.
- Before replacing, turn off power and let lamp cool to avoid electrical shock or burn.

**CAUTION:** Risk of electric shock— do not use where directly exposed to water.

**NOTES:** This device complies with Part 15 of the FCC rule. Operation is subject to the following two conditions: (1) this device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation. This Class B digital apparatus complies with Canadian ICES-005. Any changes or modifications not expressly approved by the party responsible for compliance could void the user's authority to operate the equipment. This Class B complies with Canadian ICES-005.

### Footnotes:

1. Early initial qualification for Energy Star allows for directional lamp life claims of 25,000 hours (L70) with 3,000 hour actual test data, LM80 data and in-situ temperature measurements. As the lamps pass Energy Star requirements, manufacturers may increase the lifetime of a product as dictated by Energy Star guidelines. See [http://www.energystar.gov/index.cfm?fuseaction=products\\_for\\_partners.showLightbulbs](http://www.energystar.gov/index.cfm?fuseaction=products_for_partners.showLightbulbs) for further details. Based on average usage of 3 hrs/day, 7 days/week.
2. Based on photometric testing consistent with IES LM-79. Maximum Beam Candlepower.
3. MC/CP=MasterClass or CorePro
4. Dimmable when using leading and trailing edge dimmers. (See <http://www.philips.com/ledtechguide> for compatible dimmers.)

 This lamp is ENERGY STAR® Certified.

### Footnotes from front:

- \* Early initial qualification for Energy Star allows for directional lamp life claims of 25,000 hours (L70) with 3,000 hour actual test data, LM80 data and in-situ temperature measurements. As the lamps pass Energy Star requirements, manufacturers may increase the lifetime of a product as dictated by Energy Star guidelines. See [http://www.energystar.gov/index.cfm?fuseaction=products\\_for\\_partners.showLightbulbs](http://www.energystar.gov/index.cfm?fuseaction=products_for_partners.showLightbulbs) for further details.
- ‡ For details, please visit [www.signify.com/warranties](http://www.signify.com/warranties)
- † Light output comparison based upon the ENERGY STAR® Integral LED Lamp Center Beam Intensity Benchmark tool which can be found at [EnergyStar.gov/LEDbulbs\\_LED](http://EnergyStar.gov/LEDbulbs_LED)

