



# T8 Standard

## F32T8/TL830/ALTO 30PK

Philips T8 lamps are energy-efficient lighting solutions.

### Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050

### Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Features	ALTO® (ALTO)
Flux measurement reference	Sphere

  

Light Technical	
Color Code	830 [CCT of 3000K]
Beam Angle (Nom)	0 degree(s)
Color Designation	TL830
Chromaticity Coordinate X (Nom)	443
Chromaticity Coordinate Y (Nom)	408
Correlated Color Temperature (Nom)	3000 K
Color rendering index (CRI)	≥80

  

Operating and Electrical	
Power Consumption	32.5 W
Lamp Current (Nom)	265 mA
Wattage Equivalent	32 W
Voltage (Nom)	137 V
Voltage (Nom)	137 V

Controls and Dimming	
Dimmable	Yes

  

Mechanical and Housing	
Bulb Finish	Coated glass
Bulb Shape	T-8 (T8)

  

Approval and Application	
Energy Saving Product	Energy Saving
Mercury (Hg) Content (Max)	1.7 mg
Mercury (Hg) Content (Nom)	1.7 mg
Energy Consumption kWh/1000 h	32.6 kWh

  

Product Data	
Order product name	F32T8/TL830/ALTO 30PK
Order code	582049
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	30
Material number (12NC)	927803783005
Net weight	0.136 kg
Full product name	F32T8/TL830/ALTO 30PK

## T8 Standard

EAN/UPC - Case

50046677582048

### Dimensional drawing

Product	C (max)	D (max)
F32T8/TL830/ALTO 30PK	1,213.6 mm	27.9 mm

