



# Pulse Start Metal Halide Standard

## MS1000/BU/BT37/PS 6PK

Philips Pulse Start Metal Halide Lamps offer an optimized metal halide system for greater efficiency and lumen maintenance.

### Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050

### Product data

General information	
Base	E39 [ Single Contact Mogul Screw]
Operating Position	Base Up +/- 10 D [ Base Up +/- 10 D]
Main Application	General Lighting (G)
ANSI Code HID	M141/E
System Description	Base-Up
Light technical	
Color Code	640 [ CCT of 4000K]
Design Mean Lumens	96000 lm
Chromaticity Coordinate X (Nom)	0.385
Chromaticity Coordinate Y (Nom)	0.390
Correlated Color Temperature (Nom)	4000 K


Color Rendering Index (Nom)	65
Operating and electrical	
Power (Rated) (Nom)	1000 W
Lamp Current (Nom)	4.1 A
Ignition Supply Voltage (Min)	440 V
Re-Ignition Time (Min) (Max)	15 min
Ignition Time (Max)	120 s
Voltage (Nom)	836 V
Mechanical and housing	
Bulb Finish	Clear
Cap-Base Information	Brass [ Brass Cap]

## Pulse Start Metal Halide Standard

Bulb Material	Hard Glass
Bulb Shape	BT37 [ BT37]
<b>Approval and application</b>	
Mercury (Hg) Content (Nom)	151 mg
<b>Product data</b>	
Order product name	MS1000/BU/BT37/PS 6PK

EAN/UPC - Product	046677360191
Order code	360198
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	928601132003
Net Weight (Piece)	0.002 lb

### Dimensional drawing



MS1000/BU/BT37/PS 6PK

#### Product

MS1000/BU/BT37/PS 6PK

