



CorePro LED PLS

CorePro LED PLS 5W 840 2P G23

The Philips CorePro LED PLS integrates a LED light source into a traditional fluorescent form factor. This product is the ideal solution for uplampping in general lighting applications: it meets basic lighting requirements, offers significant energy savings, and is environment-friendly.

Product data

General information	
Base	G23 [G23]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	30000 h
Switching Cycle	50000X
Flux measurement reference	Sphere
Light technical	
Color Code	841 [CCT of 4100K (841)]
Beam Angle (Nom)	120 °
Initial lumen (Nom)	550 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	110.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	82
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	5 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s


Power Factor (Nom)	0.9
Voltage (Nom)	220-240 V
Temperature	
T-Ambient (Max)	113 °F
T-Ambient (Min)	-4 °F
T-Storage (Max)	149 °F
T-Storage (Min)	-40 °F
T-Case Maximum (Nom)	181.4 °F
Controls and dimming	
Dimmable	No
Mechanical and housing	
Bulb Material	Plastic
Product Length	6.7 in
Bulb Shape	Tube, single-ended
Approval and application	
Energy Efficiency Class	F
Energy Saving Product	Yes
Approbation Marks	TUV CE marking RoHS compliance KEMA Keur certificate

CorePro LED PLS

Energy Consumption kWh/1000 h	5 kWh
EPREL Registration Number	403567
Product data	
Order product name	CorePro LED PLS 5W 840 2P G23
EAN/UPC - Product	8718699596682
Order code	367078

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	20
Material Nr. (12NC)	929001926402
Copy Net Weight (Piece)	0.095 lb


Dimensional drawing




CorePro LED PLS 5W 840 2P G23

Product	D	D1	A1	A2	A3
CorePro LED PLS 5W 840 2P G23	1-1/4 in	5/8 in	4-1/4 in	5-11/16 in	6-9/16 in


Photometric data



LEDtube CorePro PLS EM 5W G23 840 12D ND





LEDtube CorePro PLS EM 5W G23 840 12D ND



LEDtube CorePro PLS EM 5W G23 830 12D ND



CorePro LED PLS

Lifetime




LEDtube CorePro PLS EM 5W G23 830 12D ND

LEDtube CorePro PLS EM 5W G23 830 12D ND



LEDtube CorePro PLS EM 5W G23 830 12D ND

LEDtube CorePro PLS EM 5W G23 830 12D ND



LEDtube CorePro PLS EM 5W G23 830 12D ND

