



CorePro LEDcapsule MV

CorePro LEDcapsuleMV 2.6-25W G9 827 D UK

This single-ended mains-voltage capsule for G9-base luminaires delivers directional light, making it a true alternative to halogen capsule lamps. It is particularly suitable for task lighting in shops, hotels and restaurants, and ideal for desk lamps and cabinet lighting. Compatible with existing fixtures with G9 holders and designed for retrofit replacement of halogen capsules, CorePro LEDcapsule delivers huge energy savings and minimizes maintenance costs, without any compromise on light quality.

Product data

General information		Lamp Current (Nom)	
Base	G9 [G9]		14.5 mA
EU RoHS compliant	Yes	Wattage Equivalent	25 W
Nominal Lifetime (Nom)	15000 h	Starting Time (Nom)	0.5 s
Switching Cycle	50000X	Warm Up Time to 60% Light (Nom)	0.5 s
		Power Factor (Nom)	0.7
		Voltage (Nom)	220-240 V
Light technical		Temperature	
Color Code	827 [CCT of 2700K]	T-Case Maximum (Nom)	186.8 °F
Initial lumen (Nom)	300 lm		
Color Designation	Warm White (WW)	Controls and dimming	
Correlated Color Temperature (Nom)	2700 K	Dimmable	Yes
Luminous Efficacy (rated) (Nom)	115.00 lm/W	Mechanical and housing	
Color Consistency	<6	Bulb Shape	Capsule
Color Rendering Index (Nom)	80	Approval and application	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Energy Efficiency Class	E
		Suitable For Accent Lighting	No
Operating and electrical			
Input Frequency	50 to 60 Hz		
Power (Rated) (Nom)	2.6 W		

CorePro LEDcapsule MV


Energy Consumption kWh/1000 h	3 kWh
EPREL Registration Number	374868

Product data

Order product name	CorePro LEDcapsuleMV 2.6-25W G9 827 D UK
EAN/UPC - Product	8718699766696
Order code	366351

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	929002389999
Copy Net Weight (Piece)	0.026 lb


Dimensional drawing




CorePro LEDcapsuleMV 2.6-25W G9 827 D UK

Product	D	C
CorePro LEDcapsuleMV 2.6-25W G9 827 D UK	15 mm	52 mm


Photometric data



LEDcapsule MV 2,6W G9 827




LEDcapsule MV 2,6W G9 827



LEDcapsule MV 2,6W G9

CorePro LEDcapsule MV

Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram

