

# T8

## 12T8/COR/48-830/MF17/G 10/1

Philips MainsFit (UL Type B) CorePro T8 LED tubes deliver high-quality, flicker free performance at an affordable price. The UL Type B LED tubes are designed with easy installation and long-term maintenance simplicity in mind. Upgrade your lighting to Philips and realize 50,000 hour LED lifetime backed by a 5-year, full replacement limited warranty. The DLC 5.1 listed products are compatible with Philips new PTB15D emergency driver meeting UL 924 requirements.

### Product data

General Information	
Base	G13 [ Medium Bi-Pin Fluorescent]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	50000 h
Switching Cycle	50000X
Technical Type	12-32W
Light Technical	
Color Code	830 [ CCT of 3000K]
Beam Angle (Nom)	240 °
Initial lumen (Nom)	1700 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	141.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	12 W

Lamp Current (Max)	102 mA
Lamp Current (Min)	48 mA
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
UL Type	Type B - bypass the ballast
Power Factor (Nom)	0.9
Voltage (Nom)	120-277 V
Temperature	
T-Ambient (Max)	45 °C
T-Ambient (Min)	-20 °C
T-Storage (Max)	65 °C
T-Storage (Min)	-40 °C
T-Case Maximum (Nom)	70 °C
Controls and Dimming	
Dimmable	Limited
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Glass

# T8


Product Length	48 in
Bulb Shape	Tube, double-ended
<b>Approval and Application</b>	
Energy Saving Product	Yes
Approbation Marks	RoHS compliance UL certificate DLC compliance
Energy Consumption kWh/1000 h	- kWh

## Product Data

Order product name	12T8/COR/48-830/MF17/G 10/1
--------------------	-----------------------------

EAN/UPC - Product	046677563486
Order code	563486
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929002484004
Net Weight (Piece)	0.215 kg
Model Number	9290024840


## Dimensional drawing



TLED T8 120-277V 12-32W 1700lm 3000K G13


Product	D1	D2	A1	A2	A3
12T8/COR/48-830/MF17/G 10/1	25.7 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm

## Photometric data




General Uniform Lighting  
1 x TLED 12W 830K 1700lm G13  
120-277V  
12-32W  
1700lm  
3000K  
G13

LEDtube COR 12W G13 1700lm 830




LEDtube COR 12W G13 1700lm 830

Photometric data




LEDtube COR 9,9W G13 1550lm


Lifetime




LEDtube 50K-LED



LEDtube 50K FailureRate-LED




LEDtube COR 9,9W 50K LumenVsTc



LEDtube 50K-LMP

Lifetime



LEDtube 50K LifetimeVsTc-LED

