



LED Corn Cobs

54CC/LED/840/LS EX39 G3 BB 3/1

Philips Corn Cob LED replacement lamps are perfect LED replacement for a variety of outdoor applications. High intensity illumination, which means you get added visibility for applications like streets, public areas, and much more for a fraction of the energy used by conventional HID.



Product data

| General Information | |
|---------------------------------------|----------------------------------|
| Base | EX39 [Exclusionary Mogul Screw] |
| EU RoHS compliant | Yes |
| Nominal Lifetime (Nom) | 50000 h |
| Switching Cycle | 50000X |
| Light Technical | |
| Color Code | 841 [CCT of 4100K (841)] |
| Initial lumen (Nom) | 7800 lm |
| Color Designation | Cool White (CW) |
| Correlated Color Temperature (Nom) | 4000 K |
| Luminous Efficacy (rated) (Nom) | 144.00 lm/W |
| Color Consistency | ANSI 4000K quadrangle |
| Color Rendering Index (Nom) | 80 |
| LLMF At End Of Nominal Lifetime (Nom) | 70 % |
| Operating and Electrical | |
| Input Frequency | 50 to 60 Hz |
| Power (Rated) (Nom) | 54 W |
| Lamp Current (Nom) | 600 mA |
| Wattage Equivalent | 250 W |
| Starting Time (Nom) | 1 s |
| Warm Up Time to 60% Light (Nom) | 1 s |

| UL Type | Type B - bypass the ballast |
|---------------------------------|--------------------------------|
| Power Factor (Nom) | 0.9 |
| Voltage (Nom) | 100-277 V |
| Temperature | |
| T-Case Maximum (Nom) | 65 °C |
| Controls and Dimming | |
| Dimmable | Only with specific dimmers |
| Mechanical and Housing | |
| Bulb Finish | Clear |
| Bulb Shape | Corncob |
| Product Data | |
| Order product name | 54CC/LED/840/LS EX39 G3 BB 3/1 |
| EAN/UPC - Product | 046677564216 |
| Order code | 564211 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 3 |
| Material Nr. (12NC) | 929002999604 |
| Net Weight (Piece) | 0.777 kg |

LED Corn Cobs

Lifetime



50K

50K

