



LED Wallpack Retrofits

60WP/LED/840/LS EX39 G3 BB 3/1

Philips LED HID replacement lamps are perfect LED replacement for a variety of outdoor applications. High intensity illumination, which means you get added visibility for applications like streets, public areas, and much more for a fraction of the energy used by conventional HID.

Product data

General Information	
Base	EX39 [Exclusionary Mogul Screw]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	50000 h
Switching Cycle	50000X
Light Technical	
Color Code	841 [CCT of 4100K (841)]
Initial lumen (Nom)	8700 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	145.00 lm/W
Color Consistency	ANSI 4000K quadrangle
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	60 W
Lamp Current (Nom)	666 mA


Wattage Equivalent	250 W
Starting Time (Nom)	1 s
Warm Up Time to 60% Light (Nom)	1 s
UL Type	Type B - bypass the ballast
Power Factor (Nom)	0.9
Voltage (Nom)	100-277 V
Temperature	
T-Case Maximum (Nom)	65 °C
Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	Wall Pack
Product Data	
Order product name	60WP/LED/840/LS EX39 G3 BB 3/1
EAN/UPC - Product	046677564285

LED Wallpack Retrofits

Order code	564286
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	3
Material Nr. (12NC)	929003000304

Net Weight (Piece)	0.936 kg
--------------------	----------



Dimensional drawing



wallpack lamp LED 60W EX39 850 CL Dim

Product	D	C
60WP/LED/840/LS EX39 G3 BB 3/1	92 mm	270 mm


Photometric data



LEDForce LS EX39 60W WallPack EX39 840-GUL

LEDForce LS EX39 60W WallPack EX39 840-POC



LEDForce LS EX39 60W WallPack EX39 840-GUL



LEDForce LS EX39 40W WallPack EX39-LDD

LED Wallpack Retrofits

Lifetime



50K

50K

