



MASTER Glass LED bulbs

MAS LEDBULBDT3.4 -40W E27 927 A60 FR G

Featuring a classic heritage design, these filament MASTER glass bulbs combine the familiar shapes of incandescent glass LED bulbs with the benefits of long-lasting LED technology. Ideal for creating a cozy atmosphere for customers, these glass LED bulbs provide excellent quality of light. MASTER glass bulbs can be dimmed for different lumen levels and color temperatures (dimmable glass led bulbs). They also deliver significant energy savings, using 30% less energy compared to normal LED bulbs. By offering a lifetime of 25,000 hours, these dimmable glass LED bulbs also reduce maintenance costs.

Product data

| General information | |
|----------------------------|------------|
| Base | E27 [E27] |
| EU RoHS compliant | Yes |
| Nominal Lifetime (Nom) | 25000 h |
| Switching Cycle | 20000X |
| Flux measurement reference | Sphere |

| Light technical | |
|---------------------------------------|-------------------------------|
| Color Code | 922-927 [CCT of 2200K-2700K] |
| Initial lumen (Nom) | 470 lm |
| Color Designation | Warm Glow(WG) |
| Correlated Color Temperature (Nom) | 2200 2700 K |
| Luminous Efficacy (rated) (Nom) | 138.00 lm/W |
| Color Consistency | <6 |
| Color Rendering Index (Nom) | 90 |
| LLMF At End Of Nominal Lifetime (Nom) | 70 % |

| Operating and electrical | |
|---------------------------------|-------------|
| Input Frequency | 50 to 60 Hz |
| Power (Rated) (Nom) | 3.4 W |
| Lamp Current (Nom) | 24 mA |
| Wattage Equivalent | 40 W |
| Starting Time (Nom) | 0.5 s |
| Warm Up Time to 60% Light (Nom) | 0.5 s |
| Power Factor (Nom) | 0.6 |
| Voltage (Nom) | 220-240 V |

| Temperature | |
|----------------------|--------|
| T-Case Maximum (Nom) | 158 °F |

| Controls and dimming | |
|----------------------|----------------------------|
| Dimmable | Only with specific dimmers |

MASTER Glass LED bulbs

Mechanical and housing

| | |
|-------------|---------------|
| Bulb Finish | Frosted |
| Bulb Shape | A60 [A 60mm] |

Approval and application


| | |
|-------------------------------|--------|
| Energy Efficiency Class | D |
| Energy Consumption kWh/1000 h | 4 kWh |
| EPREL Registration Number | 453243 |

Product data

| | |
|--------------------|--|
| Order product name | MAS LEDBulbDT3.4 -40W E27 927 A60 FR G |
|--------------------|--|

| | |
|---------------------------------|---------------|
| EAN/UPC - Product | 8719514324671 |
| Order code | 366930 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 10 |
| Material Nr. (12NC) | 929003010002 |
| Copy Net Weight (Piece) | 0.066 lb |


Dimensional drawing




MAS LEDBulbDT3.4 -40W E27 927 A60 FR G

| Product | D | C |
|--|-------|--------|
| MAS LEDBulbDT3.4 -40W E27 927 A60 FR G | 60 mm | 104 mm |

Photometric data




LEDbulb MAS SLR A60 3,4W E27 927 FR-LDD



Spectral Power Distribution Colour

MASTER Glass LED bulbs

Photometric data




© 2022 Philips Lighting N.V. Page 11

LEDbulb MAS SLR 3,4W A60 E27 927 FR-GUL

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram

