



# LED Corn Cobs

## 36CC/LED/3CCT/LS EX39 G3 BB 3/1

Philips Corn Cob LED replacement lamps are perfect LED replacement for a variety of outdoor applications. High intensity illumination, which means you get added visibility for applications like streets, public areas, and much more for a fraction of the energy used by conventional HID.


### Product data

General Information	
Base	EX39 [ Exclusionary Mogul Screw ]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	50000 h
Switching Cycle	50000X
Light Technical	
Color Code	850 [ CCT of 5000K ]
Initial lumen (Nom)	4800/5000/5000 lm
Color Designation	Daylight
Correlated Color Temperature (Nom)	3000 4000 5000 K
Luminous Efficacy (rated) (Nom)	134.00 lm/W
Color Consistency	ANSI 5000K quadrangle
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	36 W
Lamp Current (Nom)	400 mA
Wattage Equivalent	150 W
Starting Time (Nom)	1 s
Warm Up Time to 60% Light (Nom)	1 s

UL Type	Type B - bypass the ballast
Power Factor (Nom)	0.9
Voltage (Nom)	100-277 V
Temperature	
T-Case Maximum (Nom)	60 °C
Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	Corn cob
Product Data	
Order product name	36CC/LED/3CCT/LS EX39 G3 BB 3/1
EAN/UPC - Product	046677570460
Order code	570465
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	3
Material Nr. (12NC)	929003065204
Net Weight (Piece)	0.655 kg

# LED Corn Cobs



## Dimensional drawing



Corn lamp LED 36W MultiCCT EX39 CL Dim

Product	D	C
36CC/LED/3CCT/LS EX39 G3 BB 3/1	85 mm	215 mm


## Photometric data



OSRAM Reference ID: 40101 Light EV Page 1/1

LEDTForce LS DLC 36W Corncob EX39 850-POC



LEDTForce LS DLC 36W Corncob EX39 850-GUL



LEDTForce LS DLC 36W Corncob EX39-LDD

# LED Corn Cobs

## Lifetime



50K

50K

