



LED PAR38

14PAR38/COR/930/F25/D/P/B/ULW/T20 6/1FB

Philips LED spots with a single optic beam, provide a clean beam that's free from shadows with beam angles from 15 and 40 degrees to suit every general lighting application.

Product data


General Information	
Base	E26 [Single Contact Medium Screw]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	25000 h
Switching Cycle	50000X
Light Technical	
Color Code	930 [CCT of 3000K]
Beam Angle (Nom)	25 °
Initial lumen (Nom)	1300 lm
Luminous Intensity (Nom)	5382 cd
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	92.00 lm/W
Color Consistency	<4
Color Rendering Index (Nom)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	14 W
Lamp Current (Nom)	136 mA
Wattage Equivalent	120 W
Starting Time (Nom)	0.5 s

Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.9
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	85 °C
Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Bulb Shape	PAR38 [PAR 4.75 inch/121mm]
Approval and Application	
Suitable For Accent Lighting	Yes
Product Data	
Order product name	14PAR38/COR/930/F25/D/P/B/ULW/T20 6/1FB
EAN/UPC - Product	046677576479
Order code	576470
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929003133804

LED PAR38

Net Weight (Piece) 0.535 kg

Dimensional drawing





T20 B PAR38 14W 1300lm 25D 3000K E26 D

Product

14PAR38/COR/930/F25/D/P/B/ULW/T20 6/1FB


Photometric data



Copyright: Photometric Data - Accurat Lighting E26 Page 1/1

LESspots BH 14W PAR38 E26 930 25D-LDD


LESspots BH 14W PAR38 E26 930 25D-ADL




LESspots BH 14W PAR38 E26 930 25D-POC

LED PAR38

Lifetime



LEDspots LED 25K



LEDspots LMP 25K

