



# LED Glass HID lamps

## 14GC/LED/840/ND E26 BB 6/1

Philips Glass HID lamps offer you an easy, short-payback LED solution to replace High Intensity Discharge (HID) lamps. Thanks to our High-Power LED filament technology, this new generation of indoor/outdoor glass lamps brings all the energy-efficiency and long-lifetime benefits of LED to HID replacement, while providing instant savings with a low initial investment. They are designed to have the same aesthetics, lamp size and light distribution as the HID lamps they are replacing, so the upgrade to LED is easier than ever!

### Product data

General information	
Base	E26 [ Single Contact Medium Screw]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	25000 h
Switching Cycle	15000X
Technical Type	LEDTECH-LOV
Light technical	
Color Code	841 [ CCT of 4100K (841)]
Beam Angle (Nom)	300 °
Initial lumen (Nom)	2000 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	142.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and electrical	
Input Frequency	50 to 60 Hz

Power (Rated) (Nom)	14 W
Lamp Current (Nom)	126.5 mA
Wattage Equivalent	70 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
UL Type	HIB_UL Type B (UL Listed+Classified)
Power Factor (Nom)	0.9
Voltage (Nom)	120-277 V
Temperature	
T-Case Maximum (Nom)	50.4 °C
Controls and dimming	
Dimmable	No
Mechanical and housing	
Bulb Finish	Frosted
Bulb Material	Glass
Bulb Shape	ED-23 1/2 [ ED-23 1/2]


# LED Glass HID lamps

## Product data

Order product name	14GC/LED/840/ND E26 BB 6/1
EAN/UPC - Product	046677578824
Order code	578823
Numerator - Quantity Per Pack	1

Numerator - Packs per outer box	6
Material Nr. (12NC)	929003507504
Copy Net Weight (Piece)	0.3 lb


## Dimensional drawing




14GC/LED/840/ND E26 BB 6/1

Product	D	C
14GC/LED/840/ND E26 BB 6/1	3 in	7-1/4 in


## Photometric data



General uniform lighting





Light Distribution Diagram



Spectral Power Distribution Colour

# LED Glass HID lamps

## Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram

