



DuraMax Reflector Flood

30R20/LL 120V 12/1 TP

Philips DuraMax® Long Life Reflector Flood Bulbs reduce the hassle of replacing light bulbs every few months, since all DuraMax products last longer than standard incandescent light bulbs. Available in a variety of sizes and wattages. Use flood lights for general or ambient lighting; use spot lights to highlight artwork or architecture. Both are ideal for use in recessed cans or track lighting fixtures.

Product data

General Information	
Base	E26 [Single Contact Medium Screw]
Operating Position	Universal [Universal]
Footnote Incandescent 1	Do not allow hot bulb to come in contact with liquid or metal parts of the fixture, as glass may shatter. Do not use outdoors. Do not operate in close proximity to flammable materials or those adversely affected by heat or drying. Operate only in heat resistant sockets. (87)

Light Technical	
Beam Description	Flood [Flood]

Operating and Electrical	
Power (Rated) (Nom)	30 W
Voltage (Nom)	120 V

Mechanical and Housing	
Bulb Finish	Reflector
Cap-Base Information	Aluminium [Aluminium Cap]
Filament Shape	CC6 [Straight]

Product Data	
Order product name	30R20/LL 120V 12/1 TP
EAN/UPC - Product	046677167530
Order code	167536
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	923304736316
Net Weight (Piece)	28.060 g

DuraMax Reflector Flood

Dimensional drawing

Product

30R20/LL 120V 12/1 TP

30W E26 120V R20

