



Halogen reflector

DDL 150W 20V 24PK

Philips' halogen reflector lamps offer the ideal no-fuss solution for a wide variety of medical, projection and scientific illumination systems. Their proven reliability makes them ideal for retrofit installations. The burners are precisely aligned for optimal light performance. Dichroic reflectors ensure heat dissipation towards the back of the optical system, which helps the optical system remain within temperature limits. A special blue-filter version blocking out unwanted light above 700 nm is available for dental curing applications. In addition, you get all the proven advantages of halogen technology such as a CRI of 100 – the same as natural sunlight for the best possible color rendering. Halogen lamps also create a comfortable warm white light, and they maintain their high lumen output with almost no lumen reduction throughout their lifetime.

Product data


General Information		Operating and Electrical	
Base	GX5.3 [GX5.3]	Power (Rated) (Nom)	150 W
Philips Code	14501	Voltage (Nom)	20 V
ANSI Code	DDL	Controls and Dimming	
LIF Code	-	Dimmable	Yes
Operating Position	S105 [s105]	Mechanical and Housing	
Main Application	Projection	Cap-Base Information	na [-]
Life to 50% Failures (Nom)	500 h	Bulb Material	Quartz-UV Open
J Code	-	Reflector Finish	Facetted
Light Technical		Filament Shape	-
Luminous Flux (Rated) (Nom)	400 lm	Filament Dimensions WxH	-
Correlated Color Temperature (Nom)	3150 K	Luminaire Design Requirements	
Color Rendering Index (Nom)	100	Bulb Temperature (Max)	900 °C

Halogen reflector

Pinch Temperature (Max)	350 °C
Working Distance WD	165 mm
Product Data	
Order product name	DDL 150W 20V 24PK
EAN/UPC - Product	8711500410610
Order code	315093

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	24
Material Nr. (12NC)	923921419794
Net Weight (Piece)	0.026 kg

Dimensional drawing



14501 150W GX5.3 20V

Product	D (max)	C (max)
DDL 150W 20V 24PK	50.7 mm	44.5 mm

