



Appliance Oven Tubular

APP 25W E14 230-240V T25 CL OV 1CT

Tubular vacuum lamps with clear glass (T-bulb)

Product data

General Information	
Base	E14 [E14]
Operating Position	Universal [Universal]
Main Application	Oven
Nominal Lifetime (Nom)	1000 h
Switching Cycle	4000X
Light Technical	
Initial lumen (Nom)	172 lm
Luminous Flux (Rated) (Nom)	172 lm
Correlated Color Temperature (Nom)	2700 K
Color Rendering Index (Nom)	100
Operating and Electrical	
Power (Rated) (Nom)	25.0 W
Lamp Current (Nom)	0.11 A
Starting Time (Nom)	0.0 s
Warm Up Time to 60% Light (Nom)	instant full light
Power Factor (Nom)	1
Voltage (Nom)	230-240 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Approval and Application	
Energy Efficiency Label (EEL)	E
Energy Consumption kWh/1000 h	25 kWh
Product Data	
Order product name	Appliance 25W E14 230-240V T25 CL OV 1CT
EAN/UPC - Product	8711500038715
Order code	250811
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	100
Material Nr. (12NC)	924198244440
Net Weight (Piece)	10.500 g
ILCOS Code	IBT/C-25-230/240-E14-25*

Appliance Oven Tubular

Dimensional drawing

Product	D (max)	C (max)
Appliance 25W E14 230-240V T25 CL OV 1CT	25 mm	57 mm



APP 25W E14 230-240V T25 CL OV

