



# T8 Plus

## F17T8/TL830/PLUS/ALTO 30PK

Philips PLUS T8 lamps are energy-efficient lighting solutions and offer long life.

### Warnings and Safety

• Lamp contains mercury. Manage in Accord with Disposal Laws. See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050

### Product data

General Information		Mechanical and Housing	
Base	G13 [ Medium Bi-Pin Fluorescent]	Cap-Base Information	Green Base
Life 12-Hr Programstart [Hrs]	42000 h	Nominal Length (Inch)	24
Life 12-Hr Instant Start [Hrs]	36000 h		
Life 3-Hr Program Start [Hrs]	36000 h		
Life 3-Hr Instant Start [Hrs]	30000 h		
Features	ALTO® Plus		
Light Technical		Approval and Application	
Color Code	TL830 [ CCT of 3000K (830)]	Energy Saving Product	Energy Saving
Initial lumen (Nom)	1375 lm	Picogram Per Lumen Hour	43 pg/lm.h
Color Designation	TL830	Mercury (Hg) Content (Nom)	1.7 mg
Design Mean Lumens	1310 lm		
Correlated Color Temperature (Nom)	3000 K		
Color Rendering Index (Nom)	85		
Operating and Electrical		Product Data	
Power (Rated) (Nom)	17 W	Order product name	F17T8/TL830/PLUS/ALTO 30PK
		EAN/UPC - Product	046677280932
		Order code	280933
		Numerator - Quantity Per Pack	1
		Numerator - Packs per outer box	30
		Material Nr. (12NC)	927850183003
		Net Weight (Piece)	0.068 kg

# T8 Plus

## Dimensional drawing

### Product

F17T8/TL830/PLUS/ALTO 30PK



F17T8/830 24 ALTO Plus ES

