



T8 Plus

F25T8/TL830/PLUS/ALTO 30PK

Philips PLUS T8 lamps are energy-efficient lighting solutions and offer long life.

Warnings and Safety

• Lamp contains mercury. Manage in Accord with Disposal Laws. See: www.lamprecycle.org or 1-800-555-0050

Product data


General Information		Mechanical and Housing	
Base	G13 [Medium Bi-Pin Fluorescent]	Cap-Base Information	Green Base
Life 12-Hr Programstart [Hrs]	42000 h	Nominal Length (Inch)	36
Life 12-Hr Instant Start [Hrs]	36000 h		
Life 3-Hr Program Start [Hrs]	36000 h		
Life 3-Hr Instant Start [Hrs]	30000 h		
Features	ALTO® Plus		
Light Technical		Approval and Application	
Color Code	TL830 [CCT of 3000K (830)]	Energy Saving Product	Energy Saving
Initial lumen (Nom)	2150 lm	Picogram Per Lumen Hour	28 pg/lm.h
Color Designation	TL830	Mercury (Hg) Content (Nom)	1.7 mg
Design Mean Lumens	2045 lm		
Correlated Color Temperature (Nom)	3000 K		
Color Rendering Index (Nom)	85		
Operating and Electrical		Product Data	
Power (Rated) (Nom)	25 W	Order product name	F25T8/TL830/PLUS/ALTO 30PK
		EAN/UPC - Product	046677280970
		Order code	280974
		Numerator - Quantity Per Pack	1
		Numerator - Packs per outer box	30
		Material Nr. (12NC)	927851183002
		Net Weight (Piece)	0.102 kg

T8 Plus

Dimensional drawing

Product

F25T8/TL830/PLUS/ALTO 30PK



F25T8/830 36 ALTO Plus ES

