



PLUS T8 High Output

F96T8/TL850/PLUS/HO/ALTO 25/1

Philips PLUS T8 High Output 8-foot fluorescent lamps reduce the impact on the environment by offering long life and low mercury.

Warnings and Safety

• Lamp contains mercury. Manage in Accord with Disposal Laws. See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Base	R17D [R17d (RDC)]
Life 3-Hr Start [Hrs]	24000 h
Features	ALTO® Plus
Light Technical	
Color Code	TL850 [CCT of 5000K (850)]
Initial lumen (Nom)	8100 lm
Color Designation	TL850
Design Mean Lumens	7525 lm
Correlated Color Temperature (Nom)	5000 K
Color Rendering Index (Nom)	85
Operating and Electrical	
Power (Rated) (Nom)	86 W
Mechanical and Housing	
Cap-Base Information	Green Base


Nominal Length (Inch)	96
Approval and Application	
Energy Saving Product	Energy Saving
Picogram Per Lumen Hour	24 pg/lm.h
Mercury (Hg) Content (Nom)	4.4 mg
Product Data	
Order product name	F96T8/TL850/PLUS/HO/ALTO 25/1
EAN/UPC - Product	046677236892
Order code	236893
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	927874085005
Net Weight (Piece)	0.001 kg

PLUS T8 High Output

Dimensional drawing

Product

F96T8/TL850/PLUS/HO/ALTO 25/1



F96T8 86W/850 HO ALTO Plus

