



# PL-L Long 4-Pin Base

## PL-L 36W/841/4P

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.

### Warnings and Safety

· Lamp contains mercury. Manage in Accord with Disposal Laws. See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050

### Product data


General Information		Lamp Current (Nom)		0.435 A
Base	2G11 [ 2G11]	Voltage (Nom)	106 V	
Life to 50% Failures (Nom)	15000 h	<b>Controls and Dimming</b>		
Life to 50% Failures Preheat (Nom)	20000 h	Dimmable	Yes	
<b>Light Technical</b>		<b>Mechanical and Housing</b>		
Color Code	841 [ CCT of 4100K (841)]	Bulb Finish	Silicon	
Initial lumen (Nom)	2900 lm	Cap-Base Information	4P	
Color Designation	Cool White (CW)	<b>Product Data</b>		
Lumen Maintenance 10000 h (Nom)	92 %	Order product name	PL-L 36W/841/4P	
Lumen Maintenance 2000 h (Nom)	94 %	EAN/UPC - Product	046677345136	
Lumen Maintenance 5000 h (Nom)	93 %	Order code	345132	
Correlated Color Temperature (Nom)	4100 K	Numerator - Quantity Per Pack	1	
Luminous Efficacy (rated) (Nom)	80 lm/W	Numerator - Packs per outer box	25	
Color Rendering Index (Nom)	82	Material Nr. (12NC)	927904508421	
<b>Operating and Electrical</b>		Net Weight (Piece)	104.000 g	
Power (Rated) (Nom)	36.0 W			

# PL-L Long 4-Pin Base

ILCOS Code

FSD-36/40/1B-E-2G11


## Dimensional drawing




Product	D (max)	D1 (max)	C (max)
PL-L 36W/841/4P	39.0 mm	18.0 mm	416.6 mm

PL-L 36W/840/4P Silicon

## Photometric data



LDPB\_PLLSIL\_840-Spectral power distribution B/W



LDPO\_PLLSIL\_840-Spectral power distribution Colour

